Surface Mount **Bandpass Filter**

50Ω 1215 to 1285 MHz

The Big Deal

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package

Generic photo used for illustration purposes only CASE STYLE: MP1766

Product Overview

CBP-1250C+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in aviation, mobile radio, broadband and fixed wireless.

Key Features

Feature	Advantages					
High Selectivity	The CBP-1250C+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.					
Low Passband VSWR	This filter maintains typical VSWR over passband frequency range making this filter easier to inte- grate into receiver and transmitter RF chains with less concerns for in band frequency ripple.					
Rugged construction	The CBP-1250C+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.					

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





Surface Mount **Bandpass Filter**

50Ω

1215 to 1285 MHz


Features

- · Low Insertion loss
- High selectivity
- · Miniature shielded package


Applications

- · Traffic collision avoidance system (TCAS)
- · Aeronautical radio navigation
- · Fixed satellite
- Radio astronomy
- · Radar and navigation system

Functional Schematic



Typical Frequency Response





CASE STYLE: MP1766 Electrical Specifications at 25°C


Para	meter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit		
	Center Frequency	_	—	_	1250	_	MHz		
Pass Band	Insertion Loss	F1-F2	1215-1285	_	0.8	2	dB		
	VSWR	F1-F2	1215-1285	-	1.2	—	:1		
Stop Bond Lower	Insertion Loss	DC-F3	DC-1055	20	30	_	dB		
Stop Band, Lower VSWR DC-F3 DC-1055 —	20	-	:1						
Stop Band, Upper	Insertion Loss	F4-F5	1510-2500	20	30	_	dB		
	VSWR	F4-F5	1510-2500	_	20	—	:1		


Maximum Ratings									
Operating Temperature	-40°C to 85°C								
Storage Temperature	-55°C to 100°C								
RF Power Input	5W								

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Typical Terrormance Data at 25 0									
Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)					
1	103.53	1737.18	1215	5.23					
970	51.48	49.64	1218	5.18					
1055	31.64	36.20	1223	5.07					
1115	15.08	19.76	1226	5.01					
1136	8.79	10.31	1230	4.96					
1150	5.18	5.52	1234	4.90					
1168	2.33	2.58	1237	4.86					
1187	1.28	1.60	1240	4.84					
1215	0.92	1.23	1245	4.80					
1226	0.87	1.16	1250	4.76					
1250	0.81	1.02	1255	4.75					
1275	0.82	1.08	1258	4.74					
1285	0.83	1.08	1261	4.73					
1331	2.26	2.69	1265	4.74					
1350	5.07	6.26	1268	4.75					
1390	13.22	24.83	1272	4.76					
1510	31.48	49.64	1276	4.78					
1725	59.97	46.96	1280	4.82					
2100	52.89	44.55	1283	4.86					
2500	46.78	39.49	1285	4.89					





1255 1265

1215 1225 1235 1245 FREQUENCY (MHz)

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B M174392 CBP-1250C+ EDU1782 URJ 200811 Page 2 of 3

1285





Generic photo used for illustration purposes only


Bandpass Filter



Pad Connections

INPUT	1
OUTPUT	10
GROUND	2,3,4,5,6,7,8,9,11,12,13

Demo Board MCL P/N: TB-684+ Suggested PCB Layout (PL-373)




NOTES:

TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L	M	N	
. 750	.750	.210	. 139	.157	.215	.160	.218	.157	. 100	.060	.069	. 149	
19.05	19.05	5.33	3.53	3.99	5.46	4.06	5.54	3.99	2.54	1.52	1.75	3.78	
P . 790 20.07	Q .541 13.74	R . 790 20.07	S .499 12.67	T .384 9.75	U .203 5.16	V .080 2.03	W .069 1.75	X .630 16.00	Y .630 16.00	Z .145 3.68		wt, grams 4.6	

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and mendes thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits