

## Surface Mount

# Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω DC to 6 GHz

## The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



## Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA in greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

### Notes


- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Surface Mount Bandpass Filter

50Ω 1280 to 1360 MHz

## CBP-1320Q+



Generic photo used for illustration purposes only  
CASE STYLE: HQ2299

### Features

- Broad stopband performance up to 20 GHz
- High selectivity
- Miniature shielded package

### Applications

- Aviation
- Mobile radio
- Broadband
- Radar and navigation systems

### Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1320	-	MHz
	Insertion Loss	F1-F2	1280-1360	1.9	3.0	dB
	VSWR	F1-F2	1280-1360	1.5	1.7	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-900	50	60	dB
		F3-F4	900-1170	20	35	dB
	VSWR	DC-F4	DC-1170	-	20	:1
Stop Band, Upper	Insertion Loss	F5-F6	1490-1700	20	30	dB
		F6-F7	1700-3000	45	50	dB
		F7-F8	3000-20000	-	20	dB
	VSWR	F5-F8	1490-20000	-	8	:1

### Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	8 W Max.

Passband rating, derate linearly to 3.5W at 85°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

### Functional Schematic



### Typical Frequency Response







### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
10	73.58	442.37	1280	8.85
100	89.96	255.06	1284	8.66
900	62.98	22.46	1288	8.49
1170	36.39	22.08	1292	8.34
1180	32.63	21.79	1296	8.21
1210	18.51	16.41	1300	8.11
1240	3.13	2.04	1304	8.03
1280	1.87	1.36	1308	7.97
1320	1.70	1.08	1312	7.94
1360	1.92	1.31	1316	7.91
1400	4.80	3.04	1320	7.89
1440	21.17	11.05	1324	7.89
1470	30.62	13.15	1328	7.88
1490	35.75	13.91	1332	7.89
1700	61.12	7.55	1336	7.91
3000	73.63	25.27	1340	7.94
6075	19.94	3.80	1344	7.98
10000	39.52	12.64	1348	8.04
15000	37.22	4.96	1352	8.11
20000	40.47	1.27	1360	8.35

### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




## Pad Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7,9,10,11,12,13,14

## Demo Board MCL P/N: TB-1006+ Suggested PCB Layout (PL-543)

SUGGESTED MOUNTING CONFIGURATION FOR  
HQ2218 & HQ2299 CASE STYLE "14FL01" PIN CODE






### NOTES:

- TRACE WIDTH IS SHOWN FOR FR4, IT180A WITH DIELECTRIC THICKNESS .025" ± .002". COPPER: 1/2 Oz EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

## Outline Drawing



Suggested Layout,  
Tolerance to be within ±.002

## Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K
-	-	Min	Max	-	-	-	-	-	-
.365	1.360	.240	.270	.483	1.200	.305	.150	.118	.100
9.27	34.54	6.10	6.86	12.27	30.48	7.75	3.81	3.00	2.54
L	M	N	P	Q	R	S	T	U	Wt.
.180	1.400	.405	.153	.285	.263	.120	.155	.275	grams
4.57	35.56	10.29	3.87	7.24	6.67	3.05	3.94	6.99	5.0

Note: Please refer to case style drawing for details

### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)