Surface Mount

Coaxial-Ceramic Resonator Filters and Multiplexers

DC to 6 GHz 50Ω

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Low profile designs with min. height of 0.120"
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' Coaxial-Ceramic Resonator filters offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency as high as 20 GHz.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document

A. Performance and quality attributes and continuous not expenses y stated in this specification occurrent are interned to be excluded and to find form a part or this specification as B. Electrical specifications and performance data contained in this specification document are becomen the part of the specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

50Ω 1320 to 1480 MHz

CBP-1400BD+



Generic photo used for illustration purposes only CASE STYLE: LW1611-1


Features

- · High rejection
- Minimal Insertion loss variation over operating temperature
- · Low-profile shielded package


Applications

- · Wireless medical telemetry
- · Radio astronomy
- · Aeronautical radio navigation
- · Defense systems

Functional Schematic



Typical Frequency Response



+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	-	-	-	1400	-	MHz
Pass Band	Insertion Loss	F1-F2	1320 - 1480	-	2.1	3.0	dB
	VSWR	F1-F2	1320 - 1480	-	1.32	1.67	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 1050	60	70	-	dB
		F3-F4	1050 - 1224	20	27	-	dB
Cton Bond Illanor	Incomtion Loop	F5-F6	1570 - 1700	20	25	-	dB
Stop Band, Upper	Insertion Loss	F6-F7	1700 - 2300	50	55	-	dB


Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	5 W Max. at 25°C					


Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)
1	103.41	171.66	1320	7.11
100	99.89	442.63	1330	6.69
1050	71.69	57.55	1340	6.37
1215	30.56	21.86	1350	6.12
1224	26.82	18.45	1360	5.94
1288	3.05	1.20	1370	5.81
1320	1.98	1.07	1380	5.71
1350	1.69	1.06	1390	5.65
1400	1.48	1.04	1400	5.63
1450	1.51	1.07	1410	5.65
1480	1.76	1.30	1424	5.70
1514	3.27	1.74	1428	5.72
1570	26.07	26.35	1432	5.75
1585	31.73	32.39	1436	5.79
1600	37.16	37.46	1440	5.84
1700	58.96	57.01	1444	5.90
2000	57.71	84.08	1448	5.97
2100	58.00	86.28	1452	6.05
2200	58.82	84.88	1470	6.55
2300	60.12	71.33	1480	6.92









Notes


Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	1
OUTPUT	7
GROUND	2,3,4,,5,6,8,9,10


Demo Board MCL P/N: TB-1100+ Suggested PCB Layout (PL-634)

SUGGESTED MOUNTING CONFIGURATION FOR LW1611-1 CASE STYLE




NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

Α	В	С	D	Е	F	G	Н	J	K	L	M
-	-	-	-	-	-	-	-	-	-	-	-
.435	.560	.120	.060	.170	.100	.140	.280	.040	.050	.160	.244
11.05	14.22	3.05	1.52	4.32	2.54	3.56	7.11	1.02	1.27	4.06	6.19
N	Р	Q	R	S	Т	U	V	W	X	Υ	
-	-	-	-	-	-	-	-	-	-	-	Wt.
.355	.080	.380	.090	.420	.340	.600	.235	.355	.475	.295	grams
8.51	2.03	9.65	2.29			15.24			12.07		1.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp