CBP-1400F+

1300 to 1500 MHz 500



Generic photo used for illustration purposes only CASE STYLE: KV1710

# **The Big Deal**

- Excellent Rejection
- Low passband Insertion Loss
- Miniature shielded package

## **Product Overview**

CBP-1400F+ is a ceramic-coaxial-resonator based bandpass filter in a shielded package fabricated using SMT technology. This filter offers outstanding close in rejection, low insertion loss and high power handling for use in broadband, wireless medical telemetry, fixed wireless and radio astronomy.

# **Key Features**

Feature	Advantages					
High Selectivity	The CBP-1400F+ filter incorporates High-Q ceramic resonators that enables sharp rejection near passband.					
Low Passband VSWR	This filter maintains typical VSWR over a wide passband frequency range making this filter easier to integrate into receiver and transmitter RF chains with less concerns for in band frequency ripple.					
Rugged construction	The CBP-1400F+ has been qualified over wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles.					

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited arranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

50Ω 1300 to 1500 MHz

## CBP-1400F+



Generic photo used for illustration purposes only CASE STYLE: KV1710

#### Electrical Specifications at 25°C

Parai	meter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	-	-	-	1400	-	MHz
Pass Band	Insertion Loss	F1-F2	1300-1500	-	0.8	2.0	dB
	VSWR	F1-F2	1300-1500	-	1.4	1.92	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC-1090	20.0	30.0	-	dB
Stop Ballu, Lowel	VSWR	DC-F3	DC-1090	-	20.0	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	1740-2450	20.0	30.0	-	dB
Stop Baild, Opper	VSWR	F4-F5	1740-2450	-	20.0	-	:1

Maximum Ratings								
Operating Temperature	-40°C to 85°C							
Storage Temperature	-55°C to 100°C							
RF Power Input	10 W max.							

Permanent damage may occur if any of these limits are exceeded.


#### **Features**

- · Low Insertion loss
- High selectivity
- Miniature shielded package


### **Applications**

- Wimax
- · Defense systems
- · Radio astronomy
- Space operation / Space research
- Aviation and aeronautical
- · Wireless medical telemetry

#### **Functional Schematic**




#### **Typical Frequency Response**





+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


## Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)		
1 400	97.53 87.78	1737.18 217.15	1300 1310	4.19 4.09		
1000	73.92	41.37	1320	4.00		
1090	31.38	31.60	1330	3.91		
1115	21.38	23.81	1340	3.83		
1130	14.90	16.11	1350	3.77		
1150	6.59	5.79	1360	3.71		
1160	3.75	3.15	1370	3.67		
1190	1.41	1.47	1380	3.62		
1300	0.79	1.14	1390	3.58		
1400	0.73	1.17	1400	3.55		
1500	0.74	1.03	1410	3.53		
1550	1.44	1.92	1420	3.53		
1570	3.04	3.65	1430	3.53		
1600	7.73	10.56	1440	3.54		
1635	14.23	22.87	1450	3.55		
1670	20.21	30.49	1460	3.59		
1740	30.54	36.20	1470	3.64		
1980	84.33	45.72	1480	3.69		
2450	51.46	52.65	1500	3.86		









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

#### **Pad Connections**

INPUT	1_
OUTPUT	12
GROUND	2,3,4,5,6,7,8,9,10,11,13,14,15,16,17

#### Demo Board MCL P/N: TB-693+ Suggested PCB Layout (PL-378)




- TRACE WIDTH IS SHOWN FOR OAK (OAK-602) WITH DIELECTRIC THICKNESS .022"±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
   BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

#### **Outline Drawing**



#### Outline Dimensions (inch)

1.050	.875	.239	.125	.160	.160	G . <b>278</b> 7.06	.205	.160	.070	.150	.090	.130
P 1.090	Q .870					.870				Z . <b>458</b>		Wt.
27.69	22.10	23.24	15.88	18.03	17.65	22.10	9.91	2.79	1.78	11.63		8.5

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

