

Frequency Mixer

HJK-ED9605/1

Level 21 (LO Power + 21 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TTT167

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _u)	10		2530	MHz
	RF (f _L to f _u)	10		2530	MHz
	IF	10		480	MHz
Conversion Loss	Mid band		6.1		dB
	Total Range		6.8		dB
LO-RF Isolation	Low Range		45		dB
	Mid Range		40		dB
	Upper Range		37		dB
LO-IF Isolation	Low Range		59		dB
	Mid Range		48		dB
	Upper Range		41		dB
Input IP3			+26		dBm
1 dB Compression			+15		dBm

Note: Low Range = [f_L to 10f_L]
Mid band = [2f_L to f_u/2]

Mid Range = [10f_L to f_u/2]

Upper Range = [f_u/2 to f_u]

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	3
RF	1
IF	2
GROUND	4,5,6