Surface Mount Directional Coupler

75 Ω , 13dB coupling, 5 to 1500 MHz

Features

- very flat couplingvery broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- VHF/UHF receivers/transmitters
- cellular
- catv

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		5		1500	MHz	
	5-50		0.9	1.4		
Mainline Level	50-500	50-500 1.0		1.5		
Mainline Loss ¹	500-1000		1.1	1.6	dB	
	1000-1500		1.4	2.2		
Naminal October	5-1000		13.5±0.5		dB	
Nominal Coupling	1000-1500		13.6±0.5			
	5-1000			±0.6	dB	
Coupling Flatness(±)	1000-1500			±0.8		
	5-50	17	21			
Discoticity	50-500	14	19			
Directivity	500-1000	_	18		dB	
	1000 -1500	_	17			
VOND ²	5-1000		1.3		dB	
VSWR ²	1000-1500		1.3			
	5-50			0.5		
Input Power	50-500			1.0		
-	500-1000 1000-1500			1.0 1.0		

1. Includes theoretical coupled power loss of 0.21 dB at 13 dB coupling.

2. For coupled port VSWR above 500 MHz, 1.6:1 typ.

Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.


Product Marking




Pin Connections

Function	Pin Number		
INPUT	3		
OUTPUT	4		
COUPLED	1		
GROUND	2		
ISOLATE (DO NOT USE)	6		

Electrical Schematic





REV. A M151107 ED-8967A/1 DBTC-13-5-75X+ WZ/CP/AM 190821 Page 1 of 2

DBTC-13-5-75X+



Generic photo used for illustration purposes only CASE STYLE: AT1667-1


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500, 1000, 2000

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


circuits.com


DBTC-13-5-75X+



Outline Dimensions (inch)


A	B	C	D	E	F
.150 3.81	.150 3.81	.150 3.81	.050 1.27	.030 0.76	.025 0.64
G	н	J	к		wt
.028	.050	.160	.030		grams
0.71	1.27	4.06	0.76		0.10





Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
. ,				In	Out	Cpl
5.00	0.83	13.09	21.69	20.33	25.83	21.73
10.00	0.80	13.06	21.61	21.17	28.18	22.73
30.00	0.80	13.06	21.61	21.55	29.45	23.06
50.00	0.81	13.07	21.48	21.61	29.48	22.74
70.00	0.83	13.09	21.51	21.69	29.33	22.2
100.00	0.85	13.11	21.42	21.72	28.86	21.33
500.00	0.91	13.23	20.04	17.98	19.17	12.1
700.00	0.94	13.26	19.95	16.94	17.35	10.3
1000.00	1.02	13.29	21.53	16.89	16.41	8.6
1500.00	1.52	13.90	17.38	18.50	16.87	7.3



Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp