Surface Mount Directional Coupler

DBTC-20-4L+

20dB coupling, 50Ω . 5 to 1250 MHz

Features

- very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications



Generic photo used for illustration purposes only CASE STYLE: AT1030

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

| Available Tape and Reel at no extra cost | | | | |
|--|-----------------------|--|--|--|
| Reel Size | Devices/Reel | | | |
| 7" | 20, 50, 100, 200, 500 | | | |
| 13" | 1000, 2000 | | | |

Electrical Specifications at 25°C

| Parameter | Condition (MHz) | Min. | Тур. | Max. | Unit |
|----------------------|---------------------------------|------|-----------|-------------------|------|
| Frequency Range | | 5 | | 1250 | MHz |
| Mainline Loss¹ | 5-50 | | 0.4 | 0.7 | dB |
| | 50-500 | | 0.6 | 0.9 | |
| | 500-1000 | | 0.8 | 1.2 | |
| | 1000-1250 | | 1.1 | 1.5 | |
| Nominal Coupling | 5-1250 | | 20.5 ±0.5 | | dB |
| Coupling Flatness(±) | 5-1250 | | | ±0.9 | dB |
| Directivity | 5-50 | 16 | 20 | | dB |
| | 50-500 | 13 | 19 | | |
| | 500-1000 | 7 | 11 | | |
| | 1000-1250 | 6 | 9 | | |
| VSWR ² | 5-1000 | | 1.4 | | dB |
| Input Power | 5-50 | | | 0.5 | w |
| | 50-500 500-1000 1000-1250 | | | 1.0 1.0 1.0 | |

^{1.} Includes theoretical coupled power loss of 0.04 dB at 20 dB coupling.

Maximum Ratings


| Parameter | Ratings | | |
|-----------------------|----------------|--|--|
| Operating Temperature | -40°C to 85°C | | |
| Storage Temperature | -55°C to 100°C | | |

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


| Function | Pin Number | | |
|----------------------|------------|--|--|
| INPUT | 3 | | |
| OUTPUT | 4 | | |
| COUPLED | 1 | | |
| GROUND | 2 | | |
| ISOLATE (DO NOT USE) | 6 | | |

Electrical Schematic



^{2.} For coupled port VSWR above 500 MHz, 1.6:1 typ.

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

В Α Κ .166 .155 .050 .037 .025 .012 .060 .184 .030 .004 grams .150 3.94 1.27 4.22 3.81 0.94 0.64 0.30 1.52 4.67 0.76 0.10 0.10

Demo Board MCL P/N: TB-279 Suggested PCB Layout (PL-151)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC


(SOLDER MASK OVER BARE COPPER)





DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

| Frequency (MHz) | Mainline Loss (dB) In-Out | Coupling (dB) In-Cpl | Directivity (dB) | Return Loss (dB) In Out Cpl | | |
|--------------------|---------------------------------|----------------------------|---------------------|-----------------------------------|-------|-------|
| 20.00 | 0.33 | 20.30 | 19.79 | 28.00 | 30.48 | 26.85 |
| 100.00 | 0.35 | 20.25 | 22.11 | 29.28 | 31.80 | 27.18 |
| 200.00 | 0.38 | 20.28 | 23.36 | 29.12 | 30.13 | 24.16 |
| 300.00 | 0.41 | 20.32 | 24.66 | 27.95 | 28.09 | 21.44 |
| 400.00 | 0.43 | 20.36 | 25.00 | 27.01 | 26.54 | 19.23 |
| 500.00 | 0.48 | 20.40 | 23.74 | 26.41 | 25.97 | 17.30 |
| 600.00 | 0.53 | 20.43 | 21.33 | 25.99 | 25.74 | 15.69 |
| 700.00 | 0.58 | 20.50 | 19.06 | 25.78 | 26.00 | 14.31 |
| 800.00 | 0.63 | 20.59 | 17.10 | 26.16 | 26.88 | 13.07 |
| 1000.00 | 0.70 | 20.94 | 14.20 | 28.41 | 29.64 | 11.03 |







Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp