DBTC-20-4X+

 50Ω , 20dB coupling, 20 to 1000 MHz

Features

- · very flat coupling
- · very broadband, multi octave
- temperature stable, LTCC base
- all welded construction
- · leads attached for better solderability
- micro miniature coupler
- aqueous washable
- protected by US Patents 6,140,887 & 6,784,521

Applications

- VHF/UHF receivers/transmitters
- cellular



Generic photo used for illustration purposes only CASE STYLE: AT1667-1

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications at 25°C

Parameter	Parameter Condition (MHz)		Тур.	Max.	Unit	
Frequency Range		20		1000	MHz	
Mainline Loss¹	20-200		0.3	1.0		
	200-500		0.4	1.0	dB	
	500-1000		0.7	1.3		
Nominal Coupling	20-1000		20.4±0.5		dB	
Coupling Flatness(±)	20-1000			±0.8	dB	
Directivity	20-200	13	21			
	200-500	14	21		dB	
	500-1000	_	16			
VSWR ²	20-1000		1.2		dB	
Input Power	20-200 200-500 500-1000			1.0 1.0 1.0	W	

^{1.} Includes theoretical coupled power loss of 0.04 dB at 20 dB coupling.

Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number		
INPUT	3		
OUTPUT	4		
COUPLED	1		
GROUND	2		
ISOLATE (DO NOT USE)	6		

Product Marking



Electrical Schematic




" ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT BOUTTES DO EROUND BE ROPTS TO GROUND




^{2.} For coupled port VSWR above 500 MHz, 1.6:1 typ.

Outline Drawing



Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #6 of the Unit


PCB Land Pattern



Outline Dimensions (inch)

F	E	D	С	В	Α
.025	.030	.050	.150	.150	.150
0.64	0.76	1.27	3.81	3.81	3.81
wt		K	J	Н	G
grams		.030	.160	.050	.028
0 10		0.76	4.06	1 27	0.71

Demo Board MCL P/N: TB-278 Suggested PCB Layout (PL-150)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 0.2. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


DENOTES PCB COPPER LAYOUT WITH SMOBC


(SOLDER MASK OVER BARE COPPER)


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)			Directivity (dB)	Return Loss (dB)		
	In-Out	In-CpI		In	Out	Cpl
20.00	0.33	20.30	19.79	28.00	30.48	26.85
100.00	0.35	20.25	22.11	29.28	31.80	27.18
200.00	0.38	20.28	23.36	29.12	30.13	24.16
300.00	0.41	20.32	24.66	27.95	28.09	21.44
400.00	0.43	20.36	25.00	27.01	26.54	19.23
500.00	0.48	20.40	23.74	26.41	25.97	17.30
600.00	0.53	20.43	21.33	25.99	25.74	15.69
700.00	0.58	20.50	19.06	25.78	26.00	14.31
800.00	0.63	20.59	17.10	26.16	26.88	13.07
1000.00	0.70	20.94	14.20	28.41	29.64	11.03







Additional Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp