New Product Announcement!

Ceramic

Dual Low Pass Filter

DLFCV-1000+

DC to 1000 MHz **50**Q

The Big Deal

- Low insertion loss
- Fast roll off
- Small size
- Dual filter in 1210 package





Product Overview

DLFCV-1000+ is a dual low pass filter which can also operate as a balanced input /output low pass filter in LTCC package. This filter has faster roll and offers low insertion loss, low VSWR and high power handling.

Kev Features

Feature	Advantages				
Faster roll off	DLFCV-1000+ is a dual low pass filter in LTCC package with 7 sections hence the roll off is faster.				
Power handling	Each filter can handle 8.5W power.				
Dual filter	Dual Filter in 1210 package, LTCC construction.				

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp



Ceramic **Dual Low Pass Filter**

1, 6

50Ω DC to 1000 MHz

Maximum Ratings


Operating Temperature	-40° to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input*	8.5W Max. at 25°C					
* Passband rating, derate linearly to 3.5W at 100°C ambient. Per-						

manent damage may occur if any of these limits are exceeded. Din Connections

Pin Connections
RF IN1, RF IN2

RF OUT1, RF OUT2	3, 4
GROUND	2, 5


Product Marking: HB



Outline Dimensions (^{inch}_{mm})

A	B	C	D	E	F	G
. 126	.098	. 059	.004	.022	.016	.039
3.2	2.5	1.50	.1	.56	.4	1.0
н -	J - -	K . 177 4.5	L .024 .6	M .059 1.5	WT.GR .03	

Demo Board MCL P/N: TB-867+ Suggested PCB Layout (PL-483)



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS (R043508) WITH DIELECTRIC THICKNESS .010*±.001*. COPPER: 1/2 02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OT THE POE IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's vebsite at www.minicircuits.com/MCLStore/terms.jsp

Features

- Low insertion loss
- Smal size
- · Excellent return loss
- · High rejection

Applications

- Military Applications
- VHF/UHF transmitters/receivers
- · Harmonic rejection
- Output of the A/D convertor
- Test and Measurement





CASE STYLE: JV1210C-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^(1,2) at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit	
	Insertion Loss	DC-F1	DC-1000	_	1.2	2.2	dB	
Pass Band	Freq. Cut-Off	F2	1280	—	3.0	—	dB	
	Amp Unbalance	DC-F1	DC-1000	—	0.1	—	dB	
	Pha Unbalance	DC-F1	DC-1000	—	3	_	deg	
	VSWR	DC-F1	DC-1000	—	1.4	_	:1	
Stop Band	Insertion Loss	F3-F4	1700-5000	24	27	_	dB	
	Cross Over Isolation	F3-F4	1700-5000	_	27	—	dB	
	VSWR	F3-F4	1700-5000	_	20		:1	

(1) In Application where DC voltage is present at either input or output ports, coupling capacitors are required. (2) Measured on Mini-Circuits Characterization Test Board TB-867+.



FREQUENCY (MHz) DC F1 F2 F3 **NSERTION LOSS (dB)**

Functional Schematic



Typical Performance Data at 25°C

F	Insertion Loss		Cross			_	Amp	Phase	Group Delay	
Freq.	Filter1	Filter2	Over Isolation	Filter1	Filter2	Freq.	Unbal.	Unbal.	Filter1	Filter2
(MHz)	(dB)	(dB)	(dB)	(:1)	(:1)	(MHz)	(dB)	(deg)	(ns)	(ns)
1.0	0.03	0.03	86.58	1.01	1.01	1.0	0.01	0.01	0.56	0.57
30.0	0.07	0.07	56.46	1.01	1.01	40.0	0.01	0.02	0.58	0.58
100.0	0.13	0.12	45.96	1.04	1.03	60.0	0.01	0.05	0.58	0.58
250.0	0.24	0.23	38.21	1.10	1.10	100.0	0.01	0.09	0.58	0.58
500.0	0.43	0.42	33.11	1.25	1.25	140.0	0.00	0.16	0.58	0.58
1000.0	1.00	1.05	30.36	1.46	1.54	200.0	0.01	0.24	0.58	0.58
1280.0	3.02	3.16	36.44	2.26	2.24	260.0	0.01	0.34	0.58	0.58
1400.0	10.79	12.85	30.56	3.93	4.25	300.0	0.01	0.38	0.59	0.59
1450.0	19.29	22.21	32.88	3.32	3.57	340.0	0.01	0.44	0.59	0.59
1500.0	33.50	35.73	38.85	3.17	3.43	460.0	0.02	0.64	0.61	0.61
1600.0	46.20	40.97	59.38	7.08	7.08	480.0	0.02	0.69	0.61	0.61
1700.0	46.78	45.32	65.50	12.88	12.65	500.0	0.02	0.73	0.61	0.62
1760.0	54.70	53.12	64.01	15.97	15.76	540.0	0.02	0.82	0.62	0.63
1800.0	49.27	47.00	63.58	17.81	17.63	600.0	0.02	0.93	0.64	0.64
1900.0	39.91	38.63	62.98	21.53	21.49	660.0	0.03	1.06	0.66	0.66
2000.0	36.56	35.71	62.46	24.14	24.28	700.0	0.03	1.20	0.67	0.68
2100.0	35.21	34.62	61.91	25.84	26.18	740.0	0.03	1.31	0.69	0.70
2500.0	36.38	36.82	73.40	29.38	30.26	800.0	0.03	1.55	0.72	0.73
3000.0	41.95	45.22	49.35	31.71	32.81	840.0	0.03	1.77	0.75	0.76
3400.0	43.88	50.90	42.63	32.46	34.79	900.0	0.04	2.11	0.80	0.81
4000.0	39.49	45.49	36.75	31.05	35.32	960.0	0.06	2.48	0.86	0.87
5000.0	33.10	37.01	31.76	27.23	31.28	1000.0	0.07	2.81	0.90	0.91


REV.B



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Performance Charts


DLFCV-1000+





Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's tandard Terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

Performance Charts







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the excusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits