

Surface Mount


Diplexer

DPLB-4254A01+

75Ω 5 to 1220 MHz
(5-42, 54-1220 MHz)

The Big Deal

- Low insertion loss, 1dB Typ.
- High rejection, 50dB Typ.
- Very good return loss, 24dB Typ.
- 75Ω Impedance
- Used for DOCSIS 3.1 standard



CASE STYLE: NU1620

Product Overview

DPLB-4254A01+ is a Low cost diplexer with the lowpass port at 5-42 MHz and highpass port at 54-1220 MHz. Good return loss combined with high out of channel rejection makes it an ideal component in cable TV and multiband radio systems.

Key Features

Feature	Advantages
Low passband insertion loss	Passband insertion loss 1dB typical ensures low signal loss through both the channels.
Good Stopband rejection	Co-channel rejection of 50dB typical ensures unwanted spurious are eliminated.
Good return loss at 5-42 and 54-1220 MHz	This makes signal transmission with very less reflection and well-matched with the adjacent component used in the system.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Diplexer

75Ω 5 to 1220 MHz (5-42, 54-1220 MHz)

Maximum Ratings

Operating Temperature -40° to 85°C

Storage Temperature -55°C to 100°C


RF Power Input 30dBm Max.

Permanent damage may occur if any of these limits are exceeded. These ratings are not intended for continuous normal operation

Pin Connections

HIGH PASS PORT	7
LOW PASS PORT	9
COMMON PORT	18
GROUND	1-6,8,10-17,19,20

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K
1.181	1.181	.280	.197	.394	.591	.787	.984	.066	.089
30.00	30.00	7.11	5.00	10.00	15.00	20.00	25.00	1.68	2.26
L	M	N	P	Q	R	S	T		
.111	.079	.071	1.221	1.221	.079	.091	.280		
2.82	2.01	1.80	31.01	31.01	2.01	2.31	7.11		
								Wt.	
								grams	3.6

Demo Board MCL P/N: TB-786+ Suggested PCB Layout (PL-435)

SUGGESTED MOUNTING CONFIGURATION FOR NU1620.
NY1998_NZ2001_PA2002_CASE STYLE "20DP01" PIN CODE



NOTES:

- TRACE WIDTH IS SHOWN FOR OAK-602 WITH DIELECTRIC THICKNESS .031"±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Features

- Low insertion loss
- 75Ω Impedance
- Good return loss
- High rejection

Applications

- Cable TV systems (DOCSIS 3.1 standard)
- Multiband radio systems



CAUTION NOTE: Open units are not recommended for use with Aqueous wash systems. Please evaluate your wash process before use.



CASE STYLE: NU1620

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

Parameter	Port	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	Low Pass	5-42	-	1.0	1.5
	High Pass	54-1220	-	1.0	1.5	dB
	Return Loss	Low Pass	5-42	21	24	-
		High Pass	54-1220	20	24	-
		Common	5-42	21	24	-
Stop Band Isolation	Low Pass	54-1220	43	50	-	dB
	High Pass	5-42	45	50	-	dB
Group Delay Variation	Low Pass	36-42	-	33	-	ns
	High Pass	54-60	-	33	-	ns
Crossover Isolation	LP-HP	42-54	25	30	-	dB

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)		RETURN LOSS (dB)	
	Low Pass Port	High Pass Port	Common Port	High Pass Port
1.0	0.00	76.13	47.68	47.14
5.0	0.05	63.21	39.14	37.66
36.0	0.40	66.16	35.82	32.41
40.0	0.61	55.59	27.32	27.54
42.0	0.81	58.69	28.07	26.51
45.0	1.89	48.69	12.96	12.61
45.8	3.05	38.19	8.49	8.44
46.4	4.73	30.35	5.82	5.76
47.3	9.21	20.18	3.43	3.10
48.6	20.12	9.71	3.30	1.59
49.5	30.68	5.22	5.44	1.20
50.0	36.57	3.69	7.50	1.07
54.0	58.12	1.01	47.59	0.58
60.0	71.60	0.62	33.58	0.41
75.0	79.36	0.41	28.77	0.34
100.0	67.17	0.34	33.95	0.33
250.0	64.72	0.32	55.94	0.23
500.0	58.19	0.39	37.81	0.18
750.0	52.63	0.47	35.95	0.22
1000.0	49.94	0.56	30.57	0.43
1100.0	49.10	0.60	26.40	0.56
1220.0	48.13	0.69	22.65	0.67

Functional Schematic









Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A
M172858
EDU2633/1
DPLB-4254A01+
URJ
190226
Page 2 of 3



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

