

MMIC SURFACE MOUNT

Power Splitter/Combiner

Mini-Circuits

THE BIG DEAL

- Wide bandwidth, 10.7 to 31 GHz
- Excellent isolation, 20 dB typ. at 21 GHz
- Excellent amplitude unbalance, 0.2 dB typ. at 21 GHz
- Small size, 5x5 mm
- Aqueous washable



EP4KA+

Generic photo used for illustration purposes only CASE STYLE: DG1677-2

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Instrumentation
- Radar
- Satellite communications
- 5G

PRODUCT OVERVIEW

Mini-Circuits' EP4KA+ is a MMIC 4-way 0° splitter/combiner designed for wideband operation from 10.7 to 31 GHz supporting many applications requiring high performance across a wide frequency range including LTE bands through phased array radars, 5G, as well as instrumentation and more. This model provides good isolation, and low phase and amplitude unbalance in a small 5 x 5mm QFN package. Manufactured using GaAs IPD technology, the EP4KA+ not only provides a repeatable performance, but also a high level of ESD protection.

KEY FEATURES

Feature	Advantages	
Wideband, 10.7 to 31 GHz	One power splitter can be used for wideband applications such as 5G, phased array radars, military and instrumentation.	
Excellent Amplitude and phase unbalance: amplitude unbalance, 0.2 dB typ. at 21 GHz phase unbalance, 7° typ. at 21 GHz	Ideal for Applications such as MIMO & phased array radars	
DC Passing	DC current passing is helpful in applications where both RF & DC need to pass through the DUT, such as antenna mounted hardware.	
Small size, 5 x 5mm QFN package	Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB.	

REV. B ECO-012188 EP4KA+ CM/JM/PS 220308



Mini-Circuits

MMIC SURFACE MOUNT

Power Splitter/Combiner

ELECTRICAL SPECIFICATIONS¹ AT 25°C

F	Parameter	Frequency (GHz)	Min.	Тур.	Max.	Unit	
Frequency Range			10.7		31	GHz	
Insertion Loss above 6.0 dB		10.7 - 13		0.4	2.1		
		13-22		0.6	2.4	dB	
		22 - 31		1.1	2.6		
		10.7 - 13	9	13.1			
Isolation		13-22	11	19.3		dB	
		22 - 31	14	21.5			
Phase Unbalance		10.7 - 13		2.7	_	+	
		13-22		4.7	_	Degree	
		22 - 31		7.8	_		
Amplitude Unbalance		10.7 - 13		0.3	0.8		
		13-22		0.2	0.8	dB	
		22 - 31		0.2	0.9		
VSWR (Port S)		10.7 - 13		1.2			
		13-22		1.3		:1	
		22 - 31		1.2			
VSWR (Port 1-4)		10.7 - 13		1.4			
		13-22		1.3		:1	
		22 - 31		1.2			
Power Handling	As a splitter	10.7-31	_	_	0.6	W	
	Per port as a combiner	10.7-31		_	0.6		

1. Tested on Mini-Circuits Test Board TB-EP4KAC+

MAXIMUM RATINGS

Parameter	Ratings
Operating temperature	-55°C to 105°C
Storage temperature	-65°C to 150°C
DC Current	100mA

Permanent damage may occur if any of these limits are exceeded.

MCL

EP4KA

index

PAD CONNECTIONS

Function	Pad Number
SUM PORT	21
PORT 1	14
PORT 2	10
PORT 3	31
PORT 4	27
GROUND	9,11,13,15,20,22,26,28,30,32 and Paddle
NOT USED, GROUND EXTERNALLY	1-8, 12, 16-19, 23-25, 29

SIMPLIFIED ELECTRICAL SCHEMATIC



Marking may contain other features or characters for internal lot control

PRODUCT MARKING

black body

model family designation



MMIC SURFACE MOUNT

Power Splitter/Combiner

Mini-Circuits


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE

	Data Table	
Performance Data	Swept Graphs	
	S-Parameter (S3P Files) Data Set (.zip file)	
Case Style	DG1677-2 Plastic package, exposed paddle; lead finish: Matte Tin	
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 & 1000 devices	
Suggested Layout for PCB Design	PL-649	
Evaluation Board	TB-EP4KA+ (Without connectors) TB-EP4KAC+ (With connectors)	
Environmental Ratings	ENV08T1	

ESD RATING

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL TEST FLOW CHART



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp