

## Gain Equalizer

EQY-8-453+

Mini-Circuits

 $50\Omega$  8dB DC to 45 GHz

#### THE BIG DEAL

- 8.2 dB Slope from DC to 45 GHz
- Small Package 2 x 2 mm MCLP
- Excellent Return Loss, 20 dB typ.
- Patent pending



Generic photo used for illustration purposes only

CASE STYLE: MC1630-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

#### **APPLICATIONS**

- Cellular Infrastructure
- 5G
- Wideband Communications
- Test Instrumentation
- Defense

#### **PRODUCT OVERVIEW**

EQY-8-453+ is an absorptive Gain Equalizer fabricated using highly repetitive GaAs IPD MMIC process incorporating resistors, capacitors and inductors having negative insertion loss slope. EQY-8-453+ has a nominal attenuation slope of 8.2 dB and is packaged in tiny 2 x 2 mm, 6-Lead MCLP<sup>TM</sup> package.

#### **KEY FEATURES**

Feature	Advantages		
Negative Insertion Loss Slope vs. Frequency	Useful for compensating negative gain slope of amplifiers, receivers, transmitters to achieve flat gain versus frequency.		
Wide range of values 3,4,5,6,7,8,9,10 dB	Enables circuit designer to change nominal insertion loss values without motherboard redesign making the EQY series ideal for select at test application.		
Wideband operation, DC to 45 GHz	Supports a wide array of applications including wireless cellular, microwave communications, satellite, defense and aerospace, medical broadband and optic applications.		
Excellent Power Handling Capability up to +30 dBm	Enables its use at the output of a variety of amplifiers		
Small Size and simple to use (2 mm x 2 mm)	As a single chip solution, the EQY series occupies less board space than a lumped or distributed element approach, minimizes component count and ensures repeatable performance over wide frequency range.		

\*GaAs IPD (Gallium Arsenide Integrated Passive Device)

REV. A ECO-014427 EQY-8-453+ GY/RS/CP 220808



**MICROWAVE** Gain Equalizer



Mini-Circuits

50Ω DC to 45 GHz 8dB

#### ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, 50Ω, UNLESS OTHERWISE NOTED.

Parameter	Condition (GHz)	Min.	Тур.	Max.	Units
Frequency Range		DC		45	GHz
Insertion Loss	0.01	9.1	9.4	9.7	
	10	7.5	7.9	8.1	
	20	_	5.3	—	dB
	30	2.4	3.0	3.4	
	40	_	1.5	_	
	45	—	1.2	—	
VSWR	0.01 -10	—	1.25	—	
	10 - 20	_	1.13	_	
	20 -30	_	1.17	_	:1
	30 - 40	_	1.23	_	
	40 - 45	_	1.33	_	

1. Measured on Mini-Circuits Characterization Test Board TB-EQY-8-453+. See Characterization Test Circuit (Fig. 1)

#### **MAXIMUM RATINGS<sup>2</sup>**

Parameter	Ratings
Operating Case Temperature	-55°C to 105°C
Storage Temperature	-65°C to 150°C
RF Input Power <sup>3</sup>	+27 dBm


Permanent damage may occur if any of these limits are exceeded.
 Derates linearly to +24 dBm at 105°C



Mini-Circuits

50Ω DC to 45 GHz 8dB

#### **SIMPLIFIED SCHEMATIC & PAD DESCRIPTION**



Function	Pad Number	Description
RF-IN	2	RF-Input pad
RF-OUT	5	RF-Output pad
GND	1,3,4,6 & Paddle	Ground

#### **CHARACTERIZATION TEST CIRCUIT**




Fig 1. Block Diagram of Test Circuit used for characterization. Test Board TB-EQY-8-453+ Conditions: Attenuation & Return Loss Pin=0 dBm

#### **PRODUCT MARKING**



Marking may contain other features or characters for internal lot control



## Gain Equalizer

Mini-Circuits

#### 50Ω 8dB DC to 45 GHz

# ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS CLICK HERE Performance Data Data Table Swept Graphs Swept Graphs Case Style MC1630-1 Plastic package, Lead finish: Matte-tin Tape & Reel F66 Standard quantities available on reel F66 7" reels with 20, 50, 100, 200, 500,1K or 2K devices Suggested Layout for PCB Design PL-663 Evaluation Board TB-EQY-8-453+ & TB-EQY-8-453C+


#### **ESD RATING**

**Environmental Ratings** 

Human Body Model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD STM 5.1 - 2001 Machine.

ENV08T1

#### **MSL TEST FLOW CHART**



NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

### Mini-Circuits