## Surface Mount

# **Monolithic Amplifier**

# DC-4 GHz

#### **Product Features**

- DC-4 GHz
- Single Voltage Supply
- Internally Matched to 50 Ohms
- Unconditionally Stable
- Low Performance Variation Over Temperature
- Transient Protected
- Aqueous washable
- Protected By US Patent 6,943,629

### Typical Applications

- Cellular/ PCS/ 3G Base Station
- CATV. Cable Modem & DBS
- Fixed Wireless & WLAN
- Microwave Radio & Test Equipment




CASE STYLE: WW107


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### **General Description**

ERA-51SM+ (RoHS compliant) is a wideband amplifier offering high dynamic range. It has repeatable performance from lot to lot. It is enclosed in an Micro-X package. ERA-51SM+ uses Darlington configuration and is fabricated using InGaP HBT technology. Expected MTTF is 450 years at 85°C case temperature.

### simplified schematic and pin description





Function	Pin Number	Description	
RF IN	1	RF input pin. This pin requires the use of an external DC blocking capacitor chosen for the frequency of operation.	
RF-OUT and DC-IN	3	RF output and bias pin. DC voltage is present on this pin; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit".	
GND	2,4	Connections to ground. Use via holes as shown in "Suggested Layout for PCB Design" to reduce ground path inductance for best performance.	

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Electrical Specifications at 25°C and 65mA, unless noted

Parameter		Min.	Тур.	Max.	Units	Cpk
Frequency Range*		DC		4	GHz	
Gain	f=0.1 GHz	17	18	19	dB	≥ 1.5
	f=1 GHz	_	17.4	_		
	f=2 GHz	14	16.1	17.2		
	f=3 GHz	_	14.8	_		
	f=4 GHz	11.5	12.5	14.5		
Magnitude of Gain Variation versus Temperature	f=0.1 GHz	_	.0012	.0024	dB/°C	
(values are negative)	f=1 GHz	_	.002	.004		
	f=2 GHz	_	.0027	.0054		
	f=3 GHz	_	.0033	.0066		
	f=4 GHz		.0043	.0086		
Input Return Loss	f=0.1 GHz		26		dB	
	f=1 GHz		29			
	f=2 GHz		32			
	f=3 GHz		28			
	f=4 GHz		25			
Output Return Loss	f=0.1 GHz		28		dB	
	f=1 GHz		24			
	f=2 GHz		21			
	f=3 GHz		24			
	f=4 GHz		21			
Reverse Isolation	f=1.0 GHz	19	22	_	dB	
Output Power @ 1 dB compression	f=0.1 GHz	_	18.3	_	dBm	≥ 1.33
·	f=1 GHz	16.5	18.1	_		
	f=2 GHz	_	17.8	_		
	f=3 GHz	_	16.9	_		
	f=4 GHz	_	14.8	_		
Saturated Output Power	f=0.1 GHz		18		dBm	
(at 3dB compression)	f=1 GHz		18			
	f=2 GHz		18			
	f=3 GHz		17			
	f=4 GHz		16			
Output IP3	f=0.1 GHz	33.5	35.1	_	dBm	≥ 1.33
	f=1 GHz	_	35.4	_		
	f=2 GHz	31	33.9	_		
	f=3 GHz	_	31	_		
	f=4 GHz	25	27.8	_		
Noise Figure	f=0.1 GHz	_	3.6	4.2	dB	≥ 1.33
	f=1GHz	_	3.7	_		
	f=2 GHz	_	3.7	4.5		
	f=3 GHz	_	3.9	_		
	f=4 GHz	_	4	5		
Group Delay	f=1 GHz		100		psec	
Recommended Device Operating Current			65		mA	
Device Operating Voltage		4.2	4.5	4.8	V	≥ 1.5
Device Voltage Variation vs. Temperature at 65mA			-3.2		mV/°C	
Device Voltage Variation vs. Current at 25°C			5.8		mV/mA	
Thermal Resistance, junction-to-case <sup>1</sup>			154		°C/W	

<sup>\*</sup>Guaranteed specification DC-4 GHz. Low frequency cut off determined by external coupling capacitors.

#### **Absolute Maximum Ratings**

Parameter	Ratings	
Operating Temperature*	-45°C to 85°C	
Storage Temperature	-65°C to 150°C	
Operating Current	85mA	
Power Dissipation	451mW	
Input Power	13dBm	

Note: Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation. 
¹Case is defined as ground leads.

<sup>\*</sup>Based on typical case temperature rise 5°C above ambient.


Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and mentions thereoner, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Wini-Circuits\*

Wini-Circuits\*

N. 11235 0003 (718) 034-4500 cales@minicircuits com.

### **Product Marking**



Markings in addition to model number designation may appear for internal quality control purposes.

#### Additional Detailed Technical Information

Additional information is available on our web site. To access this information enter the model number on our web site home page.

Performance data, graphs, s-parameter data set (.zip file)

Case Style: WW107

Plastic micro-x, .085 body diameter, lead finish: Matte-Tin

Tape & Reel: F4

7" Reels with 20, 50, 100, 200, 500, 1K devices

Suggested Layout for PCB Design: PL-075

Evaluation Board: TB-408-51+

**Environmental Ratings: ENV08T2** 

# **Recommended Application Circuit**

Test Board includes case, connectors, and components (in bold) soldered to PCB

R BIAS				
Vcc	"1%" Res. Values (ohms) for Optimum Biasing			
7	40.2			
8	53.6			
9	68.1			
10	82.5			
11	97.6			
12	113			
13	127			
14	143			
15	158			
16	174			
17	191			
18	205			
19	221			
20	237			

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warrantly and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### **ESD Rating**

Human Body Model (HBM): Class 1B (500 v to < 1000 v) in accordance with ANSI/ESD STM 5.1 - 2001


Machine Model (MM): Class M1 (< 100 v) in accordance with ANSI/ESD STM 5.2 - 1999

### **MSL Rating**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDECJ-STD-020C

No.	Test Required	Condition	Standard	Quantity
1	Visual Inspection	Low Power Microscope Magnification 40x	MIP-IN-0003 (MCT spec)	45 units
2	Electrical Test	Room Temperature	SCD (MCL spec)	45 units
3	SAM Analysis	Less than 10% growth in term of delamination	J-Std-020C (Jedec Standard)	45 units
4	Moisture Sensitivity Level 1	Bake at 125°C for 24 hours Soak at 85°C/85%RH for 168 hours Reflow 3 cycles at 260°C peak	J-Std-020C (Jedec Standard)	45 units

#### **MSL Test Flow Chart**



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp