

Engineering Development Model

Voltage Controlled Oscillator

JTOS-ED9565B/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BK377

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1980		2805	MHz
Tuning Voltage		0.5 - 16		V
Power Output		+8		dBm
Phase Noise				
at 1 kHz offset		-65		dBc/Hz
at 10 KHz offset		-90		dBc/Hz
at 100 KHz offset		-113		dBc/Hz
at 1000 kHz offset		-133		dBc/Hz
Pulling at 12 dBr PK-PK all phases		23		MHz
Pushing at Vcc ± 5%		6		MHz/V
Tuning Sensitivity		50 - 80		MHz/V
Harmonic Suppression		-15	0	dBc
3 dB Modulation Bandwidth		131000		kHz
Supply Voltage		12		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+14V
Absolute Tuning Voltage (Vtune)	+18V

PIN CONNECTIONS	
RF OUT	13
VCC	2
V-TUNE	5
GROUND	1,3,4,6,7,8,9,10,11,12,14