# **SMA Fixed Attenuator**

FW-6+

 $50\Omega$ **1W**  6dB

DC to 12000 MHz

### **Maximum Ratings**

Operating Temperature -45°C to 100°C Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded

#### **Features**

- wideband coverage, DC to 12000 MHz
- 1 watt rating
- rugged unibody construction
- · off-the-shelf availability
- very low cost

## **Applications**

- impedance matching
- · signal level adjustment

Generic photo used for illustration purposes only


CASE STYLE: FF704

Connectors Model FW-6+

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Outline Drawing**



# Outline Dimensions (inch )

В D Ε .410 1.43 .312 grams 10 41 36.32 7 92 10.0

### Electrical Specifications at 25°C


Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit
Frequency Range		DC	_	12000	MHz
	10	_	6	_	
	DC - 3000	5.6	6.2	6.7	
Attenuation	3000 - 8000	5.85	6.45	7.1	dB
	8000 - 12000	6.15	6.8	7.4	
	DC - 3000	_	1.05	1.20	
VSWR	3000 - 8000	_	1.15	1.35	:1
	8000 - 12000	_	1.30	_	
Input Power	DC - 12000	_	_	1.0	w


1. Flatness = variation over band divided by 2.


# **Typical Performance Data**

Frequency (MHz)	Attenuation (dB)	VSWR (:1)
10.00	6.03	1.02
100.00	6.06	1.02
2000.00	6.21	1.01
3000.00	6.28	1.03
6000.00	6.48	1.08
8000.00	6.61	1.13
10000.00	6.79	1.26
11000.00	6.80	1.25
11500.00	6.81	1.24
12000.00	6.82	1.23
15000.00	6.84	1.17
11000.00 11500.00 12000.00	6.80 6.81 6.82	1.25 1.24 1.23

#### **Electrical Schematic**







A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement ins.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively: "Standard Terms"): Purchases of this part. Ferrormance and updany authorities and contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp