


5 Volt, High Gain Monolithic Amplifier Die

GVA-81-D+

50Ω DC to 6 GHz

The Big Deal

- High Gain, 10 dB Typ.
- High Pout, P1dB 19.5dBm Typ.
- High IP3, 41dBm Typ. at 1GHz
- Transient protected, US patent 6,943,629



Product Overview

GVA-81-D+ (RoHS compliant) is a wideband high gain amplifier die offering high dynamic range. It uses patented Transient Protected Darlington configuration and is fabricated using InGaP HBT technology, offering flat gain over a broad frequency range and high IP3. It provides good input and output return loss over a broad frequency range without the need for external matching components. Provided as an unpackaged amplifier die on GaAs, this model allows easy integration directly into the user's hybrids.

Key Features

Feature	Advantages
Broadband, 0.1 to 6.0 GHz	Covers the primary wireless communications bands: cellular, PCS, LTE, and WiMAX
Good Gain flatness: • ±0.6 dB over 0.1 to 3 GHz • ± 1.2 dB over 0.1 to 6 GHz	Eliminates the need for gain flattening using external components.
High IP3 versus DC power consumption • +42 dBm typical at 0.1 GHz • +35 dBm typical at 3 GHz	The GVA-81-D+ matches industry leading IP3 performance relative to device size and power consumption. The combination of the design and InGaP HBT structure provides enhanced linearity over a broad frequency range, evident in IP3 values typically 15 dB above the P1dB point to 3 GHz. This feature makes this amplifier ideal for use in: • Driver amplifiers for complex waveform up converter paths • Drivers in linearized transmit systems
No External Matching Components Required	GVA-81-D+ provides input and Output return loss of >15 dB up to 6 GHz without the need for external matching components, saving real estate and reducing component count.
Unpackaged die	Enables user to integrate it directly into hybrids.

5 Volt, High Gain Monolithic Amplifier Die

GVA-81-D+

50Ω DC to 6 GHz

Product Features


- High Gain, 10 dB Typ.
- High Pout, P1dB 19.5dBm Typ.
- High IP3, 41dBm Typ. at 1GHz
- Ruggedized design
- Fixed 5V operation
- Excellent ESD Protection

Typical Applications

- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

General Description

GVA-81-D+ (RoHS compliant) is a wideband high gain amplifier die offering high dynamic range. It uses patented Transient Protected Darlington configuration and is fabricated using InGaP HBT technology, offering flat gain over a broad frequency range and high IP3. It provides good input and output return loss over a broad frequency range without the need for external matching components. Provided as an unpackaged amplifier die on GaAs, this model allows easy integration directly into the user's hybrids.




+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Ordering Information: Refer to Last Page

Simplified Schematic and Pad description



Pad#	Function
1	RF-IN
3	RF-OUT
2,4 and bottom of die	GROUND

Bonding Pad Position



Dimensions in μm , Typical

L1	L2	L3	L4	H1	H2	H3	H4
95	293	455	550	95	324	554	650

Thickness	Die size	Pad size 1 & 3	Pad size 2 & 4
100	550 x 650	95 x 95	195 x 95



Electrical Specifications¹ at 25°C and 5V, unless noted

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range ²		DC		6	GHz
Gain	0.1 1.0 2.0 3.0 4.0 6.0		10.5 10.5 10.0 9.3 8.7 8.1		dB
Magnitude of Gain Variation versus Temperature ³ (values are negative)	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	0.0005 0.0010 0.0016 0.0020 0.0025 0.0036	— — — — — —	dB/°C
Input Return Loss	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	38.0 27.0 20.1 17.4 16.9 18.5	— — — — — —	dB
Output Return Loss	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	21.4 20.6 17.4 14.5 13.1 14.8	— — — — — —	dB
Reverse Isolation	2.0		20.8		dB
Output Power @ 1 dB compression	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	19.1 19.1 19.7 20.0 19.4 17.7	— — — — — —	dBm
Output IP3	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	42.0 41.3 36.6 35.0 33.2 31.1	— — — — — —	dBm
Noise Figure	0.1 1.0 2.0 3.0 4.0 6.0	— — — — — —	7.3 7.3 7.4 7.6 7.7 8.3	— — — — — —	dB
Group Delay	2.0		98		psec
Device Operating Voltage		4.8	5.0	5.2	V
Device Operating Current		94	103	112	mA
Device Current Variation vs. Temperature			62		μA/°C
Device Current Variation vs Voltage			0.036		mA/mV
Thermal Resistance, junction-to-ground lead			68		°C/W

¹ Die is packaged in SOT-89 and soldered on characterization test board TB-313. See Characterization Test Circuit (Fig. 1)

² Low frequency cut off determined by external coupling capacitors and RF Choke (RFC).

³ (Gain at 85°C, Gain at -45°C)/130

Absolute Maximum Ratings

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Operating Current at 5V	160mA
Power Dissipation	0.855W
Input Power	13dBm
DC Voltage on Pin 3	5.9V

Notes: Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.



Characterization Test & Application Circuit





Fig 1. Block Diagram of Test Circuit used for characterization. (Measured on Mini-Circuits characterization test board. Die packaged in SOT-89 Package and soldered on test board TB-313).

Gain, Output power at 1dB compression (P1 dB) and output IP3 (OIP3) are measured using R&S Network Analyzer ZVA-24. Noise Figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

Assembly Diagram



Assembly and Handling Procedure

1. **Storage**
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. **ESD**
MMIC HBT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
3. **Die Handling and Attachment**
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
5. **Wire Bonding**
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

Additional Detailed Technical Information <i>additional information is available on our dash board.</i>	
Performance Data	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
Case Style	Die
Die Ordering and packaging information	Quantity, Package Model No. Small, Gel - Pak: 5,10,50,100 KGD* GVA-81-DG+ Medium†, Partial wafer: KGD*<2597 GVA-81-DP+ Large†, Full Wafer GVA-81-DF+
	†Available upon request contact sales representative Refer to AN-60-067
Environmental Ratings	ENV80

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1C (1000V to <2000V) accordance with ANSI/ESD STM 5.1 - 2001

** Tested in SOT-89 package.

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

