# Ceramic **High Pass Filter**

1400 to 3900 MHz 50Ω

# **The Big Deal**

- Small size 2.0 mm x 1.25 mm
- High Power handling
- High rejection
- Ceramic construction





Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

# **Product Overview**

The HFCG-1100+ LTCC High Pass Filter is constructed with 11 layers in order to achieve a miniature size and high repeatability of performance. Wrap-around terminations minimize variations in performance due to parasitics. Covering 1400-3900 MHz, these units offer low insertion loss and good rejection.

# **Key Features**

Feature	Advantages				
Small Size (2.0 mm x 1.25 mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitic.				
Wrap around termination	Provides excellent solderability and easy visual inspection capability.				
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.				

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Ceramic **High Pass Filter**

1400 to 3900 MHz 50Ω


#### **Features**

- Small size
- 7 sections
- Temperature stable
- Excellent power handling, 4W


### **Applications**


- Transmitters / Receivers
- Global positioning system(GPS)
- Satellite broadcast applications


### **Functional Schematic**




## **Typical Frequency Response**









Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
Stop Band	Dejection Loop	DC-F1	DC-530	40	53	-	dB
	Rejection Loss	DC-F2	DC-700	20	30	-	dB
	Freq. Cut-Off	F3 *	1050	-	3.0	-	dB
Pass Band	Incontion Loop	F4-F7	1400-3900	-	1.6	2.5	dB
	Insertion Loss	F5-F6	1500-3200	-	1.2	2	dB
	Return Loss	F4-F6	1400-3200	-	13	-	dB


This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details 2 Measured on Mini-Circuits Characterization Test Board TB-1090+.

\* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	4W at 25°C			
*Passband rating, derate linearly to 0.8W at 125°C ambient				

Permanent damage may occur if any of these limits are exceeded

#### Typical Performance Data at 25°C Frequency Insertion Loss **Return Loss** (MHz) (dB) (dB) 81.85 67.38 10 0.21 0.24 100 250 58.76 530 0.45 53.61 700 710 31.04 0.61 30.07 0.63 750 26.27 0.69 810 20.86 0.84 1.42 900 13.06 2.91 7.51 970 7.44 1040 3.33 1050 2.96 8.65 1100 1.78 17.21 14.36 1400 0.97 1500 0.78 18.13 2000 0.53 17.67 2500 0.44 18.98 0.37 25.57 3000 3200 3900 0.42 18.07 1.10 8.15



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# ∭Mini-Circuits

REV. A ECO-012606 HFCG-1100+ EDU3266 URJ 220331 Page 2 of 3

# HFCG-1100+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

Electrical Specifications<sup>1,2</sup> at 25°C

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

# **High Pass Filter**




#### **Pad Connections**

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

#### **Product Marking: LB**

Demo Board MCL P/N: TB-1090+ Suggested PCB Layout (PL-615)




#### NOTES:

 TRACE WIDTH IS SHOWN FOR ROGERS (R04350B) WITH DIELECTRIC THICKNESS .020"±.0015". COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

#### **Outline Drawing**



### Outline Dimensions ( inch )

Α	В	С	D	E	F	G	н	Wt.
.079	.049	.037	.014	.012	.012	.026	.025	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	0.63	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Mini-Circuits**