

HFCG-1500+

 50Ω 1600 to 6000 MHz

The Big Deal

- Small size 2.0 mm x 1.25 mm
- Very good Power handling
- Ceramic construction



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

Product Overview

HFCG-1500+ is a high pass filter with passband from 1600 MHz to 6000 MHz supporting a variety of applications. This model provides 2 dB typical insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Small size, 2.0 mm x 1.25 mm	Accommodates tight space requirements for dense PCB layouts.
Wrap around termination	Provides excellent solderability and easy visual inspection capability.
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.
Wide pass band	This filter has a wide passband from 1.6 GHz to 6 GHz.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

1600 to 6000 MHz 50Ω

Features

Small size

• Temperature stable

• LTCC construction

Applications • Transmitters / Receivers • Test and measurements · Military applications

wireless systems

• Very good power handling, 2.5W

· Telecommunications and broadband

HFCG-1500+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-9

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications(1,2) at 25°C

					u u		
Pai	Parameter		Frequency (MHz)	Min.	Тур.	Max.	Unit
	Poinction Loop	DC-F1	DC - 800	30	40	-	dB
Stop Band	Rejection Loss	F1-F2	800 - 1000	28	35	-	dB
	Freq. Cut-Off	F3 *	1400	-	3.0	-	dB
		F4-F5	1600 - 1900	-	2.0	-	dB
Pass Band	Insertion Loss	F5-F6	1900 - 5000	-	1.0	1.7	dB
		F6-F7	5000 - 6000	-	2.0	-	dB
	Return Loss	F4-F7	1600 - 6000	-	10	-	dB


- 1 This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details
- 2 Measured on Mini-Circuits Characterization Test Board TB-1104+
- Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.


Maximum Ratings			
Operating Temperature	-55°C to 125°C		
Storage Temperature	-55°C to 125°C		
RF Power Input*	2.5W at 25°C		
*B 1 1 2 1 1 2 1 1 1			


*Passband rating, derate linearly to 0.5W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.


Functional Schematic


Typical Frequency Response











Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	1
OUTPUT	3
GROUND	2, 4, 5, 6

Product Marking: LZ


Demo Board MCL P/N: TB-1104+ Suggested PCB Layout (PL-633)



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .020±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

Wt.	G	F	E	D	С	В	Α
grams	.026	.012	.012	.014	.037	.049	.079
.008	0.65	0.30	0.30	0.35	0.95	1.25	2.00

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp