HFCW-6010+

 50Ω

6400 to 20000 MHz

The Big Deal

- Very good rejection, 45 dB typical
- Small size 0603 (0.063" X 0.032" X 0.024")
- Good Power handling, 2.5W
- Ceramic construction



Generic photo used for illustration purposes only CASE STYLE: JC0603C

Product Overview

HFCW-6010+ is a high pass filter with passband from 6400 MHz to 20000 MHz supporting a variety of applications. This model provides good insertion loss over a wide band due to strategically constructed layout. Housed in a tiny 0603 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Small size, 0603 (0.063" X 0.032" X 0.024")	Accommodates tight space requirements for dense PCB layouts.
Wrap around termination	Provides excellent solderability and easy visual inspection capability.
LTCC construction	Provides a rugged package that is well suited for tough environments including high humidity and high temperature extremes.
Ultra-wide pass band	This filter has a very wide passband from 6.4 GHz to 20 GHz.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



 50Ω

6400 to 20000 MHz

HFCW-6010+



Generic photo used for illustration purposes only CASE STYLE: JC0603C

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Features

- Very good rejection, 45 dB typ.
- Small size 0603 (0.063" X 0.032" X 0.024")
- Temperature stable
- LTCC construction


Applications

- Test and measurements
- · Military applications
- Telecommunications and broadband wireless systems


Functional Schematic




Typical Frequency Response









Electrical Specifications (1,2) at 25°C

Pai	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	D :	DC-F1	DC - 3500	39	44	-	dB
Stop Band	pp Band Rejection Loss		3500 - 4900	20	34	-	dB
Freq. Cut-Off		F3	6010	-	2.8	-	dB
		F4-F5	6400 - 7700	-	2.0	-	dB
Pass Band	Insertion Loss	F5-F6	7700 - 14000	-	0.9	1.4	dB
		F6-F7	14000 - 20000	-	2.0	-	dB
	Return Loss	F4-F7	6400 - 20000	-	9	-	dB


- 1 This component is not intended to act as a DC block. Please consult with Mini-Circuits for further details
- 2 Measured on Mini-Circuits Characterization Test Board TB-HFCW-6010+

Maximum Ratings			
Operating Temperature	-55°C to 125°C		
Storage Temperature	-55°C to 125°C		
RF Power Input*	2.5W @ 25°C		

* Passband rating, derate linearly to 0.7W at 125°C ambient Permanent damage may occur if any of these limits are exce

Typical Performance Data at 25°C

Гиолизия		Detum Lees
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	69.60	0.09
100	69.37	0.13
500	54.06	0.21
2000	46.98	0.29
3000	55.53	0.32
3500	67.38	0.35
4900	37.36	0.67
5300	20.75	1.23
5500	12.93	2.19
5900	3.05	12.36
6010	2.25	18.55
6400	1.29	38.53
7000	0.86	22.47
7700	0.65	20.80
8000	0.59	21.73
10000	0.41	27.24
12000	0.38	25.09
14000	0.48	14.28
20000	0.70	16.60
23500	3.60	16.59



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

INPUT	1
OUTPUT	3
GROUND	2456

Product Marking: S


Demo Board MCL P/N: TB-HFCW-6010+ Suggested PCB Layout (PL-703)



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4350B) WITH DIELECTRIC THICKNESS .0200±.0015. COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - DENOTES PCB COPPER PATTERN WITH SMOBC (SOLDER MASK OVER BARE COPPER) DENOTES PCB COPPER PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

) E	C D)	в с	В	Α
2 .008 .	024 .012	2	.032 .024	.032	.063
0 0.20	0.60 0.30)	0.80 0.60	0.80	1.60

Note: Please refer to case style drawing for details.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

