## LFCG-1000+

 $50\Omega$ DC to 1000 MHz

## The Big Deal

- Very good rejection, 45 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

## **Product Overview**

Mini-Circuits' LFCG-1000+ is an LTCC low pass filter with a passband from DC to 1000 MHz, supporting a variety of applications. This model provides 0.8 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55°C to 125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

## **Kev Features**

Feature	Advantages			
Very good stopband rejection, 45 dB typical	The LTCC lowpass filter provides a very good stopband rejection until 10 GHz suitable for high end applications.			
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.			
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.			
Excellent power handling, 5.5W	Supports a wide range of system power requirements.			
Wrap-around terminations	Provides excellent solderability and easy visual inspection			

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Low Pass Filter**

DC to 1000 MHz  $50\Omega$ 

## LFCG-1000+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

### +RoHS Compliant

Тур.

0.8

3.0

21

30

45

35

30

Max.

1.8

Unit

dB

dB

dΒ

dΒ

dB

dB

dΒ

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Min.

20

35

30


## **Features**


- · Low loss, 0.8 dB typical
- · High rejection 45 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction

## **Applications**

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use

### **Functional Schematic**





2. Measured on Mini-Circuits Characterization Test Board TB-799+

**Parameter** 

Pass Band

Stop Band

Insertion Loss

Freq. Cut-Off

Return Loss

Rejection Loss

DC-F1

F2

DC-F1

F3-F4

F4-F5


F5-F6

F6-F7

Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

\*Passband rating, derate linearly to 1W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

# **Typical Frequency Response**



## Typical Performance Data at 25°C

Electrical Specifications<sup>1,2</sup> at 25°C

Frequency (MHz)

DC-1000

1370

DC-1000

1550-1900


1900-3000


3000-6000

6000-10000

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports.

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10 100	0.12 0.18	39.37 30.94
1000	0.74	23.43
1370	3.39	11.65
1450	9.47	7.28
1510	20.39	4.42
1550	31.51	3.12
1750	42.02	1.00
1900	59.59	0.65
2000	52.69	0.53
2500	49.74	0.32
3000	44.29	0.24
4000	38.87	0.14
5000	37.65	0.09
6000	37.95	0.11
7000	37.04	0.24
7500	49.61	0.27
8000	48.29	0.29
9000	45.40	0.32
10000	40.34	0.32







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

  B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

  C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


LFCG-1000+ **Low Pass Filter** 

## **Pad Connections**

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

### **Product Marking: KC**

Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)




### NOTES:

- 1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

## **Outline Drawing**



## Outline Dimensions (inch )

Α	В	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

