

Engineering Development Model

Level 15 (LO Power +15 dBm)

Frequency Mixer

HJK-ED11431/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click back, and then click Contact Us for Applications support



CASE STYLE: TTT167

ELECTRICAL SPECIFICATIONS 50Ω @25°C

Parameter	Min.	Typ.	Max.	Units
Frequency	LO/RF			MHz
	IF			MHz
Conversion Loss	500	6.9	2000	dB
L-R Isolation	0.5	48	550	dB
L-I Isolation		39		dB
IP3		+25		dBm
1 dB Compression		+14		dBm

MAXIMUM RATINGS

Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	+16 dBm

PIN CONNECTIONS

LO	2
RF	1
IF	3
GROUND	4,5,6

Electrical Schematic

