# Ceramic ow Pass Filter

50Ω DC to 2000 MHz

# **LFCG-2000+**

# **The Big Deal**

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 5.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

# **Product Overview**

Mini-Circuits' LFCG-2000+ is an LTCC low pass filter with a passband from DC to 2000 MHz, supporting a variety of applications. This model provides 1.0 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

# **Key Features**

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 13.5 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Excellent power handling, 5.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection.

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Ceramic Low Pass Filter

50Ω DC to 2000 MHz


#### Features

- Low loss, 1.0 dB typical
- Very good rejection 50 dB typical
- Excellent power handling, 5.5W
- Extremely small size 0805 (0.079" x 0.049" x 0.037")
- Temperature stable
- LTCC construction


## Applications

- · Military Radio applications
- · Test and measurement
- Telecommunications & broadband wireless
  applications

## **Functional Schematic**



## **Typical Frequency Response**







Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

+ROHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

# Electrical Specifications<sup>1,2</sup> at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 2000	_	1.0	1.7	dB
Pass Band	Freq. Cut-Off	F2	2350	_	3.0	_	dB
	Return Loss	DC-F1	DC - 2000	_	17	—	dB
		F3-F4	2850 - 3300	20	40	_	dB
Stop Band	Rejection Loss	F4-F5	3300 - 7500	40	52	_	dB
		F5-F6	7500 - 13500	_	28	_	dB

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2 Measured on Mini-Circuits Characterization Test Board TB-799+

#### Maximum Ratings

maximum ridings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	5.5W max.@25°C			
*Passband rating, derate linearly to 1W at 125°C ambient				

Permanent damage may occur if any of these limits are exceeded.

#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)				
10	0.09	42.73				
100	0.13	32.88				
500	0.27	22.74				
1000	0.42	19.44				
1500	0.56	23.62				
1700	0.67	34.08				
2000	0.98	21.21				
2350	2.32	14.74				
2400	3.29	9.43				
2550	11.05	2.33				
2700	24.35	1.07				
2760	30.86	0.92				
2850	43.53	0.78				
3000	50.34	0.65				
3300	63.29	0.52				
5000	72.15	0.15				
6000	65.28	0.22				
7500	52.03	0.20				
10000	36.88	0.37				
13500	29.78	0.13				



Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B ECO-007606 LFCG-2000+ EDU3836 URJ 210428 Page 2 of 3

# Low Pass Filter




#### **Pad Connections**

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

**Product Marking: MY** 

Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)




COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER

BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

#### **Outline Drawing**



### Outline Dimensions ( inch )

А	в	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Mini-Circuits**