# Ceramic ow Pass Filter

50Ω DC to 2250 MHz

# LFCG-2250+

## **The Big Deal**

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 4.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

## **Product Overview**

Mini-Circuits' LFCG-2250+ is an LTCC low pass filter with a passband from DC to 2250 MHz, supporting a variety of applications. This model provides 1.2 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55°C to 125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

## **Key Features**

Feature	Advantages			
Very good stopband rejection, 50 dB typical	The LTCC lowpass filter provides a very good stopband rejection until 15 GHz suitable for high end applications.			
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.			
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.			
High power handling, 4.5W	Supports a wide range of system power requirements.			
Wrap-around terminations	Provides excellent solderability and easy visual inspection			

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Ceramic Low Pass Filter

50Ω DC to 2250 MHz


#### **Features**

- . Low loss, 1.2 dB typical
- High rejection 50 dB typical
- Excellent power handling, 4.5W
- Extremely small size 0805 (2.0 mm x 1.25 mm)
- Temperature stable
- LTCC construction


#### **Applications**

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use

#### **Functional Schematic**



#### **Typical Frequency Response**



	Ра	rameter	F#	Frequency (MHZ)	win.	тур.	wax.	
		Insertion Loss	DC-F1	DC-2250	—	1.2	2.0	
	Pass Band	Freq. Cut-Off	F2	2500	—	3.0	_	
		Return Loss	DC-F1	DC-2250	—	21	—	
	Stop Band	Rejection Loss	F3-F4	2800-3600	20	30	—	
			F4-F5	3600-8000	35	50	_	
			F5-F6	8000-15000	_	30	_	

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2 Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	4.5 W max.@25°C			
*Passhand rating, derate linearly to 1W at 125°C ambient				

Permanent damage may occur if any of these limits are exceeded.

#### Typical Performance Data at 25°C

rypiour renormance bata at 20 0					
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)			
10	0.09	44.91			
100	0.12	41.11			
1000	0.33	22.06			
2250	1.18	41.70			
2500	3.05	14.39			
2650	13.79	3.09			
2695	20.61	2.20			
2745	30.24	1.70			
2800	36.02	1.40			
3000	40.39	0.92			
3600	41.21	0.53			
4000	45.69	0.44			
5000	54.92	0.30			
6000	52.50	0.20			
8000	50.24	0.15			
10000	40.34	0.33			
11000	35.08	0.42			
12500	30.67	0.39			
13500	28.58	0.39			
15000	26.47	0.52			



A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### ∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A ECO-004070 LFCG-2250+ EDU2887 URJ 210316 Page 2 of 3

## LFCG-2250+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Unit

dB dB

dB

dB

dB dB

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site

for RoHS Compliance methodologies and qualifications

## Electrical Specifications<sup>1,2</sup> at 25°C

## Low Pass Filter




#### **Pad Connections**

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: KF


Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)



- COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

#### **Outline Drawing**



#### Outline Dimensions ( inch )

А	В	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### **Mini-Circuits**