LFCG-2850+

 50Ω DC to 2850 MHz

The Big Deal

- Very good rejection, 45 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 4.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-2850+ is an LTCC low pass filter with a passband from DC to 2850 MHz, supporting a variety of applications. This model provides 0.9 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55°C to 125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Kev Features

| Feature | Advantages | | | | |
|---|---|--|--|--|--|
| Very good stopband rejection, 45 dB typical | The LTCC lowpass filter provides a very good stopband rejection until 14 GHz suitable for high en applications. | | | | |
| LTCC Construction | Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes. | | | | |
| Tiny size (0.079" x 0.049" x 0.037") | Saves space in dense circuit board layouts and minimizes the effects of parasitics. | | | | |
| High power handling, 4.5W | Supports a wide range of system power requirements. | | | | |
| Wrap-around terminations | Provides excellent solderability and easy visual inspection | | | | |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Pass Filter

DC to 2850 MHz 50Ω

LFCG-2850+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Unit

dB

dΒ

dB

dB

dΒ

dΒ

dΒ

Max.

1.8

+RoHS Compliant

Тур.

0.9

3.0

21

30

45

30

20

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Min.

20


35


Features

- · Low loss, 0.9 dB typical
- High rejection 45 dB typical
- Excellent power handling 4.5W
- Extremely small size 0805 (2.0 mm x 1.25 mm)
- Temperature stable
- LTCC construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use





Parameter

Pass Band

Stop Band

Insertion Loss

Freq. Cut-Off

Return Loss


Rejection Loss

*Passband rating, derate linearly to 1W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

Functional Schematic

| RF IN | RF OUT |
|----------|---------------------|
| o | · • ···· |
| # | # |
| | |
| <u>+</u> | = |

Typical Frequency Response



Typical Performance Data at 25°C

Electrical Specifications^{1,2} at 25°C

Frequency (MHz)

DC-2850

3250

DC-2850

3800-4400

4400-8000

8000-12000

12000-14000

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports.

F#

DC-F1

F2

DC-F1


F3-F4


F4-F5

F5-F6


F6-F7

Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.









A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Pad Connections

| INPUT | 8 |
|--------|--------|
| OUTPUT | 4 |
| GROUND | 123567 |

Product Marking: KG

Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)




NOTES:

- 1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch)

| Wt. | G | F | Е | D | С | В | Α |
|-------|------|------|------|------|------|------|------|
| grams | .026 | .012 | .012 | .014 | .037 | .049 | .079 |
| .008 | 0.65 | 0.30 | 0.30 | 0.35 | 0.95 | 1.25 | 2.00 |

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

