Ceramic ow Pass Filter

50Ω DC to 4800 MHz

LFCG-4800+

The Big Deal

- Very good rejection, 42 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 4.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-4800+ is an LTCC low pass filter with a passband from DC to 4800 MHz, supporting a variety of applications. This model provides 1.2 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages			
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 18 GHz suitable for high end applications.			
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.			
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.			
Excellent power handling, 4.5W	Supports a wide range of system power requirements.			
Wrap-around terminations	Provides excellent solderability and easy visual inspection			

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

50Ω DC to 4800 MHz

Features

- . Low loss, 1.2 dB typical
- Very good rejection 42 dB typical
- Excellent power handling, 4.5W
- Extremely small size 0805 (0.079" x 0.049" x 0.037")
- Temperature stable
- LTCC construction

Applications

RF IN

С

- Military Radar applications
- · Test and measurement

Functional Schematic

RF OUT

o

5G Sub 6 Telecom

LFCG-4800+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^{1,2} at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss DC-F1		DC - 4800 —		1.2	1.7	dB
Pass Band	Freq. Cut-Off	F2	5600	—	3	—	dB
	Return Loss	DC-F1	DC - 4800	—	12	—	dB
Stop Band	Rejection Loss	F3-F4	6700 - 7200	20	34	—	dB
		F4-F5	7200 - 9300	33	42	—	dB
		F5-F6	9300 - 12500	22	29	—	dB
		F6-F7	12500 - 18000	—	20	—	dB

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2 Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings Operating Temperature -55°C to 125°C Storage Temperature -55°C to 125°C **RF** Power Input* 4.5W max.@25°C *Passband rating, derate linearly to 1W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

	Typical Performance Data at 25°C				
	Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)		
Typical Frequency Response					
	10	0.08	51.01		
FREQUENCY (MHz)	100	0.09	45.43		
DC F1 F2 F3 F4 F5 F6 F7	300	0.13	40.15		
	400	0.15	39.94		
(gg)	500	0.17	40.59		
	1000	0.22	42.59		
8 VIIIII	4800	1.07	15.04		
	5440	1.93	16.27		
	5600	3.16	10.26		
	6200	23.23	1.50		
	6400	31.96	1.04		
	6700	44.87	0.67		
z V	7200	55.48	0.38		
	9000	50.78	0.26		
	9300	48.92	0.28		
	11000	36.80	0.49		
	12500	30.68	0.42		
	13000	30.01	0.42		
	15000	30.52	0.40		
	18000	23.97	0.36		



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.A ECO-006012 LFCG-4800+ EDU3850 URJ 210108 Page 2 of 3

Low Pass Filter




Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: MD


Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)



- COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch)

А	в	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits