Ceramic .ow Pass Filter

DC to 490 MHz 50Ω

LFCG-490+

The Big Deal

- Very good rejection, 45 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Good power handling, 3.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-490+ is an LTCC low pass filter with a passband from DC to 490 MHz, supporting a variety of applications. This model provides 1.5 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 3.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 8.5 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Good power handling, 3.5W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Ceramic Low Pass Filter

50Ω DC to 490 MHz


Features

- . Low loss, 1.5 dB typical
- High rejection 45 dB typical
- · Good power handling, 3.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction
- **Applications**
- Harmonic Rejection
- VHF/UHF transmitters / receivers
- · Military radar applications
- · Test and measurement
- Telecommunications & broadband wireless applications
- Satcom modems

Functional Schematic



Typical Frequency Response





Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^{1,2} at 25°C


Pa	rameter	F#	Frequency (MHz)	requency (MHz) Min. Typ.		Max.	Unit
	Insertion Loss	DC-F1	DC - 490	_	1.5	2	dB
Pass Band Freq. Cut-Off F2		590	_	3.0	—	dB	
	Return Loss	DC-F1	DC - 490	_	14	—	dB
		F3-F4	800 - 960	20	50	_	dB
Stop Bond	top Band Rejection Loss	F4-F5	960 - 1500	40	48	_	dB
Stop Banu		F5-F6	1500 - 3000	35	45	_	dB
			3000 - 8500		15	_	dB

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2. Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	3.5W max.@25°C			
*Passband rating, derate linearly to 0.9W at 125°C ambient				

Permanent damage may occur if any of these limits are exceeded. Typical Darfa rmanaa Data at 25°C

Typical Performance Data at 25°C				
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)		
10	0.22	33.05		
100	0.38	20.89		
300	0.75	16.37		
400	0.99	24.15		
490	1.46	20.86		
590	3.26	12.95		
685	20.48	3.94		
720	31.29	3.16		
800	59.71	1.83		
960	58.62	0.74		
1500	51.64	0.23		
3000	46.62	0.14		
4200	30.44	0.28		
6100	35.45	0.29		
6600	29.96	0.58		
7000	40.92	2.84		
7600	31.96	1.13		
8000	27.65	0.77		
8400	26.02	0.68		
8500	25.93	0.78		



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A ECO-007606 LFCG-490+ EDU3520 URJ 210426 Page 2 of 3




Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: LP

Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)




COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER

BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch)

W	G	F	E	D	С	В	А
gran	.026	.012	.012	.014	.037	.049	.079
.00	0.65	0.30	0.30	0.35	0.95	1.25	2.00

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp