Ceramic ow Pass Filter

50Ω DC to 530 MHz

LFCG-530+

The Big Deal

- Good rejection, 30 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 3.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-530+ is an LTCC low pass filter with a passband from DC to 530 MHz, supporting a variety of applications. This model provides 1 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 3.5W RF input power and provides a wide operating temperature range from -55°C to 125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages		
Good stopband rejection, 30 dB typical	The LTCC lowpass filter provides a good stopband rejection suitable for high end applications.		
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.		
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.		
Excellent power handling, 3.5W	Supports a wide range of system power requirements.		
Wrap-around terminations	Provides excellent solderability and easy visual inspection		

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

50Ω DC to 530 MHz


Features

- Low loss, 1dB typical
- High rejection 30 dB typical
- Excellent power handling, 3.5W
- Extremely small size 0805 (2.0mm x 1.25mm)
- Temperature stable
- LTCC construction


Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- RF suppression for DC lines on PCB
- Anti-aliasing for A/D converter

Functional Schematic



Typical Frequency Response



Electrical Specifications^{1,2} at 25°C E# Frequency (MHz) Min, Typ

	14	rarameter		ricqueriey (minz)		1.76.	INIGA.	Unit	Ĺ
		Insertion Loss	DC-F1	DC - 530	_	1.0	1.8	dB	Ĺ
	Pass Band	Freq. Cut-Off	F2	670	—	3.0	—	dB	Ĺ
		Return Loss	DC-F1	DC - 530	_	21	—	dB	Ĺ
	Stop Band Rejection Loss	Paiastian Lass	F3-F4	980 - 2600	25	30	—	dB	Ĺ
		F4-F5	2600 - 4000	_	25	_	dB	Ĺ	

1. DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports.

Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2. Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings					
Operating Temperature	-55°C to 125°C				
Storage Temperature	-55°C to 125°C				
RF Power Input*	3.5W max.@25°C				
*Deach and actions, deached line and the O.O.W. at 10500 and is at					

*Passband rating, derate linearly to 0.6W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Typical Terrormance Data at 25 0						
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)				
1	0.16	39.83				
50	0.20	35.18				
100	0.24	33.52				
250	0.37	32.91				
500	0.85	25.69				
530	0.98	23.62				
650	2.47	14.42				
670	3.28	11.75				
730	10.53	4.77				
830	20.56	1.71				
900	37.75	1.11				
980	32.03	0.78				
1000	32.17	0.72				
1500	35.01	0.27				
2000	54.73	0.19				
2600	34.12	0.16				
3000	31.11	0.14				
3500	29.45	0.13				
3750	28.99	0.13				
4000	28.62	0.15				



Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

1Mini_Circuite

w W.MINICITCUITS.COM P.O. BOX 350166, Brooklyn, NY 11235-0003 (718) 934 4500 sales@minicircuits.com REV. A ECO-007606 LFCG-530+ EDU3066 URJ 210426 Page 2 of 3

LFCG-530+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

I Incid

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Linini-Circuits							
www.minicircuits.com	PO Box 350166 Brooklyn NY 11235-0003 (718) 934-4500 sales@minicircuits.com						

Low Pass Filter




Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: KR


Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)



- COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch

А	В	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Min-Circuits and ard limited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits