

## Frequency Mixer

## HJK-ED9142/2

Level 17 (LO Power +17 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : TTT167**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f <sub>L</sub> to f <sub>U</sub> )	1690		1805	MHz
	RF (f <sub>L</sub> to f <sub>U</sub> )	1690		1805	MHz
	IF	220		295	MHz
Conversion Loss			7.5		dB
LO-RF Isolation			49		dB
LO-IF Isolation			35		dB
IP3 Input			+32		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	2
RF	1
IF	3
GROUND	4, 5, 6