

Frequency Mixer

HJK-ED9494A/1

Level 17 (LO Power + 17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-690

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	714		2089	MHz
	RF (f _L to f _U)	714		2089	MHz
	IF	10		300	MHz
Conversion Loss	Total Range		7.2		dB
LO-RF Isolation			40		dB
LO-IF Isolation			40		dB
Input IP3			+26		dBm
1 dB Compression			0		dBm

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	8
RF	4
IF	2
GROUND	1,3,6