

Frequency Mixer

HJK-ED9535/1

Level 17 (LO Power +17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : TTT167

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	118		190	MHz
	RF (f _L to f _U)	118		190	MHz
	IF	29		75	MHz
Conversion Loss	Total Range		7.0		dB
LO-RF Isolation	Low Range		47		dB
LO-IF Isolation	Low Range		44		dB
IP3 Input			+33		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	2
RF	1
IF	3
GROUND	4, 5, 6