50Ω 100W 2500 to 6000 MHz

The Big Deal

- High output power at saturation, 100W typ.
- High gain, 58 dB typ.
- Operates from AC line power: 85-264V
- Rugged design for rigorous lab applications
- Built-in over-temperature protections



CASE STYLE: NG1942

Product Overview

The HPA-100W-63+ is a high power, rack mount amplifier with a self-contained AC power supply which can be used for a wide variety of laboratory testing applications. This rugged amplifier is capable of amplifying signals up to 100W output power over its entire operating bandwidth of 2500 to 6000 MHz. Built-in safety features include fans alarms and automatic shut down mechanism to prevent damage in the event of excessive internal temperatures. The amplifier's output stage is further protected in the event of a fault condition, allowing high power operation for up to 5 minutes into an open or short load (refer to the maximum input power specifications).

Key Features

Feature	Advantages
Wideband frequency range	2500 to 6000 MHz bandwidth covers popular wireless communications, SATCOM and radar bands in a single instrument, useful for many test applications.
100W output power at saturation	Supports high power test applications such as EMI, max power handling, and reliability testing
High Gain	58 dB typical gain allows the HPA-100W-63+ to be driven to full output power with nearly all commercially available signal generators
High Reverse Isolation	Insulates load reflections to protect sensitive signal sources from potential damage and performance variation due to load pulling
A/C Power	Operating from standard AC line power supply - the HPA-100W-63+ can be powered from 85-264V at 47~63 Hz making this HPA versatile in supporting global markets
Cooling system	Front to back forced air cooling fans makes this ideal for usage in test equipment racks.
Built-in protections	The unit shuts OFF when the internal amplifier reaches a set temperature of 85±5°C, preventing damage to the amplifier and providing added reliability.
C € marked	Meets conformity standards for sale within the European Economic Area (EEA).

50Ω 100W 2500 to 6000 MHz

Features

- High output power at saturation, 100W typ.
- High gain, 58 dB typ.
- Excellent reverse isolation, 93 dB typ.
- Rugged 3U rack mount case style with internal fans
- Operates from AC line power: 85-264V
- Built-in over-temperature protections
- C € marked

Applications

- · Laboratory test instrument
- RF Power stress test
- EMI and antenna testing
- Reliability testing



CASE STYLE: NG1942

Model No. Description

HPA-100W-63+ High Power Amplifier

w/ N-Type Connectors

Included Accessories

CBL-3W-XX AC Power Cord

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Condition	Min.	Тур.	Max.	Units
Frequency Range		2500	_	6000	MHz
Gain	2500 - 6000 MHz	52	58	64	dB
Gain Flatness	2500 - 6000 MHz	_	±2.0	±3.5	dB
Output Power at 1dB compression ¹	2500 - 6000 MHz	+39	+43	_	dBm
Output Power at Saturation ¹	2500 - 6000 MHz	_	+50	_	dBm
Noise Figure	2500 - 6000 MHz	_	15	19	dB
Output third order intercept point	2500 - 6000 MHz	_	+50	_	dBm
Input VSWR	2500 - 6000 MHz	_	2.5	3.0	:1
Output VSWR	2500 - 6000 MHz	_	2.5	3.0	:1
Isolation	2500 - 6000 MHz	_	93	_	dB
Line Supply	47~63 Hz		85/264		V
Power Consumption	110/220V	_	450	600	W

^{1.} Power measured of fundamental tone only. Does not include power contribution of harmonics signals.

Maximum Ratings²

Parameter	Ratings		
Operating Temperature	0°C to 50°C		
Storage Temperature	-20°C to 70°C (non condensing)		
Innut DE Dower (no domesto)	+3 dBm³		
Input RF Power (no damage)	-15 dBm⁴		

^{2.} Specifications apply to CW signals only permanent damage may occur if any of these limits are exceeded.

D-Sub Male Connector Pin Functions (Front Panel)

Pin#	Function	TTL Logic Level			
PIII#	runction	Low	High		
1	Temperature Alarm	Normal	Alarm Shutdown		
2	Fan Alarm	Normal	Fault		
3	Ground	_	_		
4-9	No connection	_	_		

LED Indicators (Front Panel)


Name	Color	LED State			
		Off	On		
Power	Green	Power off	Power on		
Temp	Red	Normal	Alarm Shutdown		
Fan	Red	Normal	Fault		



^{3.} Into 50 ohm load

^{4.} Into open or short load, for up to 5 minutes.

Outline Drawing



Outline Dimensions (inch)

C 20.0 G H 2.25 18.31 A 5.20 K 3.49 Q 2.24 19.0 17.13 3.17 7.63 2.23 3.82 4.05 grams .13 .94 5.12 88.65 132.08 482.60 508.00 23.88 435.10 57.15 465.07 80.52 97.03 193.80 130.05 56.90 102.87 13610.0

Ordering, Pricing & Availability Information see our web site


Model	Description
HPA-100W-63+	Rack Mount High Power Amplifier


Included Accessories	Description
CBL-3W-XX	AC Power Cord (Select one power cord from below with each Rack Mount HPA)


AC Power Cords	Description	
CBL-3W-US	US Power Cord	
CBL-3W-EU	EU Power Cord	
CBL-3W-UK	UK Power Cord	


Typical	Performance	Data
----------------	-------------	------


FREQUENCY (MHz)	GAIN (dB)	ISOLATION (dB)		WR :1)	POUT at 1 dB COMPR. (dBm)	POUT at Saturation (dBm)	NOISE FIGURE (dB)	IP3 (dBm)
		IN	OUT					
2500	60.2	93.0	1.4	1.1	43.2	50.3	11.9	53.8
3000	60.4	94.0	1.6	1.0	44.2	49.1	12.2	54.0
3500	58.7	91.0	1.8	1.1	44.4	49.8	10.6	51.1
4000	59.6	114.0	1.8	1.2	42.6	49.1	10.7	51.3
4500	58.2	94.0	1.6	1.1	42.3	50.1	11.5	51.4
5000	58.3	88.0	1.2	1.1	42.7	50.1	11.6	51.1
5500	60.1	99.0	1.1	1.1	42.7	49.0	11.6	50.7
6000	58.2	93.0	1.4	1.4	43.3	48.7	11.9	50.6














Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

