Ceramic Low Pass Filter

DC¹ to 2690 MHz **50**O


Features

- Low loss, 0.8 dB typ.
- Small size 0603 (1.6 x 0.8 mm)
- Temperature stable
- LTCC construction


Applications

- Wireless communication
- Harmonic Rejection
- VHF/UHF transmitters / receivers
- Lab use

Functional Schematic



Typical Frequency Response







Generic photo used for illustration purposes only CASE STYLE: JC0603C

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^{1,2} at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC - F0	DC - 2300	—	0.8	1.2	dB
Pass Band		F0 - F1	2300 - 2690	_	0.5	0.8	dB
	Freq. Cut-Off	F2	3200	_	3.0	_	dB
	VSWR	F0 - F1	2300 - 2690	—	1.6	—	:1
Stop Band		F3	4400	—	20	—	dB
	Rejection Loss	F4 - F5	4800 - 5400	25	30	_	dB
		F6	10000	_	20	_	dB

1. In Application where DC voltage is present at either input or output port, coupling capacitors are required.


2. Measured on Mini-Circuits Characterization Test Board TB-797+

Maximum Ratings					
Operating Temperature	-55°C to 100°C				
Storage Temperature	-55°C to 100°C				
RF Power Input ³	3W at 25°C				
3. Passband rating, derate linearly to 1.5W at 100°C ambient					

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data⁴ at 25°C Insertion Loss VSWR Frequency (MHz) (dB) (:1) 10 0.11 1.01 100 0.07 1.06 500 1.33 0.18 800 0.32 1.55 1200 0.53 1 81 0.64 1500 1.93 2300 0.51 1.54 2690 0.46 1.11 2.93 3200 4.08 37.43 4400 20.61 4800 26.69 41.77 5400 31.02 46.74 59.83 6000 28.38 7000 23.15 106.88 8000 19.89 111.91 10000 14.96 33.43

4. Measured with Agilent E5071B network analyzer using port extension.



Notes

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

REV. A M151107 ED-16419/25 LFCW-272+ MY/CP/AM 200513

Mini-Circuits




Pad Connections

INPUT	6
OUTPUT	4
GROUND	2,5
NC	1,3

Product Marking: N/A


Evaluation Board MCL P/N: TB-797+ Suggested PCB Layout (PL-426)



NOTES:

- COPLANAR WAVEGIDE IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER
- BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch)

А	В	С	D	Е	F	G	wt
.063	.031	.024	.012	.008	.006	.020	grams
1.60	0.79	0.61	0.30	0.20	0.15	0.51	0.005

Notes

Notes
 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rejutes and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

