

Engineering Development Model

Voltage Controlled Oscillator

JCOS-ED7275/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BG419

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	910		990	MHz
Tuning Voltage	0.5		15	V
Power Output		+6		dBm
Phase Noise				
at 1 kHz offset		-85		dBc/Hz
at 10 KHz offset		-110		dBc/Hz
at 100 KHz offset		-130		dBc/Hz
at 1000 kHz offset		-150		dBc/Hz
Pulling at 12 dBm PK-PK all phases		5		MHz
Pushing at Vcc=5V±0.25V		0.2		MHz/V
Tuning Sensitivity		8 - 11		MHz/V
Harmonic Suppression		-30	-20	dBc
3 dB Modulation Bandwidth		2700		kHz
Supply Voltage		10		V
Supply Current			25	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+12V
Absolute Tuning Voltage (Vtune)	+17V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	1
GROUND	2,3,4,5,6,9,10,11,12,13,14