Ceramic .ow Pass Filter

DC to 6.3 GHz 50Ω

LFCW-6300+

The Big Deal

- Very good rejection, 44 dB typical
- Rugged, ceramic construction
- Tiny size, 0.063 x 0.032 x 0.024" (0603)
- Good power handling, 2.5 W



Generic photo used for illustration purposes only CASE STYLE: JC0603C-1

Product Overview

Mini-Circuits' LFCW-6300+ is an LTCC low pass filter with a passband from DC to 6.3 GHz, supporting a variety of applications. This model provides 1.6 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 2.5 W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0603 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 26.5 GHz suitable for high end applications.
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.
Tiny size (0.063 x 0.032 x 0.024")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.
Good power handling, 2.5 W	Supports a wide range of system power requirements.
Wrap-around terminations	Provides excellent solderability and easy visual inspection

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

DC to 6.3 GHz

50Ω

Features

LFCW-6300+



Generic photo used for illustration purposes only CASE STYLE: JC0603C-1


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

- Low loss, 1.6 dB typical
 Good rejection 44 dB typical
- Extremely small size 0603 (0.063 X 0.032 X 0.024")
- Temperature stable
- LTCC construction


Applications

- Military radios
- Point-Point communication
- 5G Sub 6 GHz
- WiFi
- ISM band

Functional Schematic



Typical Frequency Response



			-				
Parameter		F# Frequency (MHz)		Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 6300	_	1.6	2.1	dB
Pass Band	Freq. Cut-Off	F2*	7200	_	3.0	_	dB
	Return Loss	DC-F1	DC - 6300	—	13	_	dB
Stop Band	Rejection Loss	F3-F4	8600 - 9300	20	42	_	dB
		F4-F5	9300 - 14300	30	44	_	dB
		F5-F6	14300 - 18300	25	34	_	dB
		F6-F7	18300 - 26500	_	25	_	dB

Electrical Specifications^{1,2} at 25°C

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required.

2 Measured on Mini-Circuits Characterization Test Board TB-LFCW-6300+


* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings			
Operating Temperature	-55°C to 125°C		
Storage Temperature	-55°C to 125°C		
RF Power Input*	2.5 W @25°C		
*Peeeband rating denote linearly to 0.9 W at 125°C ambient			

*Passband rating, derate linearly to 0.8 W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Typical Fertorniance Data at 25 C				
Frequency (MHz)				
10	0.09	41.02		
100	0.10	37.66		
500	0.19	29.52		
1000	0.25	27.35		
2000	0.36	22.66		
3000	0.47	20.13		
6000	1.16	16.63		
6300	1.35	15.36		
7200	2.65	14.42		
7300	3.27	11.20		
7700	11.05	2.55		
8000	21.00	1.28		
8250	30.36	0.98		
8600	47.29	0.81		
9300	54.97	0.70		
10000	54.92	0.64		
14300	39.93	0.43		
18300	34.34	0.43		
20000	33.52	0.33		
26500	26.87	0.85		



Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B ECO-014416 LFCW-6300+ EDU3822 URJ 220803 Page 2 of 3




Pad Connections

INPUT	1
OUTPUT	3
GROUND	2, 4

Product Marking: L


Demo Board MCL P/N: TB-LFCW-6300+ Suggested PCB Layout (PL-650)



NOTES:

- 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS (RO4835 Lo Pro) WITH DIELECTRIC THICKNESS .0107±.0010. COPPER: 1/2 Oz. EACH SIDE.
- FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

Outline Drawing



Outline Dimensions (inch)

А	в	С	D	Е	F	G	Wt.
.063	.032	.024	.018	.028	.006	.012	grams
1.60	0.80	0.60	0.45	0.70	0.15	0.30	.005

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp