

# Frequency Mixer

## LRMS-ED6326/2

Level 10 (LO Power +10 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : QQQ569

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1		1970	MHz
	RF (fL to fU)	1		1970	MHz
	IF	3		900	MHz
Conversion Loss	mid band		6.9		dB
	Total Range		7.5		dB
LO-RF Isolation	Low Range		-		dB
	Mid Range		63		dB
	Upper Range		29		dB
LO-IF Isolation	Low Range		-		dB
	Mid Range		50		dB
	Upper Range		29		dB

**Note:** Low Range = [fL to 10fL]      Mid Range = [10fL to fU/2]      Upper Range = [fU/2 to fU]  
mid band = [2fL to fU/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	1
RF	4
IF	5
GROUND	2, 3, 6