

Frequency Mixer

JMS-ED5689/2

Level 7 (LO Power +7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BH292

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	175		2193	MHz
	RF (f _L to f _U)	175		2193	MHz
	IF	1		1000	MHz
Conversion Loss	mid band		7.4		dB
	Total Range		8.1		dB
LO-RF Isolation	Low Range		28		dB
	Mid Range		-		dB
	Upper Range		25		dB
LO-IF Isolation	Low Range		41		dB
	Mid Range		-		dB
	Upper Range		42		dB

Note: Low Range = [f_L to 10f_L] Mid Range = [10f_L to f_U/2] Upper Range = [f_U/2 to f_U]
mid band = [2f_L to f_U/2]

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	6
RF	3
IF	2
GROUND	1, 4, 5