

Engineering Development Model

Power Splitter/Combiner

JSPQ-ED8004/1

2 Way-90°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BK276

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		6		90 MHz
Isolation	6 - 60 MHz		42	dB
	45 - 90 MHz		41	dB
Insertion Loss Average of Coupled Outputs above 3.0 dB	6 - 60 MHz		0.45	dB
	45 - 90 MHz		0.80	dB
Phase Unbalance	6 - 60 MHz		0.268	deg.
	45 - 90 MHz		0.582	deg.
Amplitude Unbalance	6 - 60 MHz		0.135	dB
	45 - 90 MHz		0.243	dB
VSWR	SUM Port		1.18	(:1)
	OUT Ports		1.29	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	7
PORT 2	8
GND EXT	2, 3, 4, 5, 6, 9, 10, 11, 12, 13, 14

Functional Diagram

