Ultra Wideband, Flat Gain **Monolithic Amplifier Die**

50Ω DC to 50 GHz

The Big Deal

- Ultra Wideband, DC to 50 GHz
- Excellent Gain Flatness, ±2.2 dB over 0.1 to 50 GHz
- May be used as a replacement model for MAAM-011109-DIE^{a,b}



Product Overview

The LTA-M1109-D+ is an ultra-wideband distributed amplifier die that provides medium gain and excellent gain flatness over DC to 50GHz. It is fabricated using PHEMT process that delivers exceptional broadband RF performance. The amplifier has good P1dB and OIP3 performance. And it is also well-matched to 50Ω , requiring no external matching circuits to achieve published performance.

Kev Features

Feature	Advantages
Ultra Wideband: DC to 50GHz	General purpose wideband amplifier is suitable for various applications
Medium Gain • 17.3 dB at 0.1GHz • 17.4 dB at 45 GHz	Minimizes the number of gain stages required to achieve published gain, reducing component count, cost and complexity.
Good P1dB • 20.7 dBm at 0.1GHz • 17.9 dBm at 30GHz	Useful as a driver amplifier. Can be used as a final amplifier in local oscillator chains to drive 17dBm mixers.
Unpackaged die	Enables user to integrate it directly into hybrids.

Notes:

a. Suitability for model replacement within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application and compatibility with other

components and environmental conditions and stresses. b. The MAAM-011109-DIE part number is used for identification and comparison purposes only.

Ultra Wideband, Flat Gain Monolithic Amplifier Die

LTA-M1109-D+

50 Ω DC to 50 GHz

Product Features

- Ultra Wideband, DC-50 GHz
- Excellent Gain Flatness, ±2.2dB over 0.1 to 50 GHz
- May be used as a replacement model for MAAM-011109-DIE^{a,b}

Typical Applications

- 5G
- Point-to-point Radio
- Military
- Instrumentation

	VOET	ar
		ve L
EL-AMP-13	w	


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

General Description


The LTA-M1109-D+ is an ultra-wideband distributed amplifier die that provides medium gain and excellent gain flatness over DC to 50GHz. It is fabricated using PHEMT process that delivers exceptional broadband RF performance. The amplifier has good P1dB and OIP3 performance. And it is also well-matched to 50Ω , requiring no external matching circuits to achieve published performance.

Simplified Schematic and Pad description



Pad #	Function	Description				
1	RF-IN	RF Input Pad				
3	VGG	Gate Bias Pad				
4&11	VC	Gain Control Pads				
6	RF-OUT & VDD	RF Output and Drain Pad				
8	VDET Voltage Detector Pad					
9	VD	Alternative Drain Bias Pad, connects to Pad#6 internally.				
10	VD1	Alternative Drain Bias Pad. It is terminated by C2				
2,5,5,7 & Bottom of die	GROUND	Connects to ground				

Bonding Pad Position



Dimensions in µm, Typical																	
L1	L2	L3	L4	L5	L6	L7	L8	H1	H2	НЗ	H4	H5	H6	H7	H8	H9	H10
88	112	363	520	1040	1285	1882	1970	89	341	471	601	633	841	971	1101	1211	1300

Thickness	Die size	Pad size 1,6	Pad size 2,5,7,12	Pad size 3,8,9,10&11	Pad size 4
100	1970 x 1300	73 x 113	91 x 86	93 x 73	73 x 93

REV. B ECO-006624 LTA-M1109-D+ GY/RS/CP 210302 Page 2 of 5

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

JMini-Circuits



Electrical Specifications¹ at 25°C, VC=Open, Zo=50Ω at T_{AMB}=25°C

Condition (MHz)	$V_{pp} = 5V, I_{pp} = 1$		A	Units
	Min.		Max.	
	DC		50	GHz
100		17.3		dB
10000				
				dB
				42
				dB
				GD
				dB
				dBm
				abiii
				dBm
				abiii
				dB
				42
				V
				V
		160.0		mA
1		1 100.0		
		-0.24		mA
	100	Min. 100 DC 10000 20000 30000 40000 50000 100 10000 20000 30000 40000 50000 100 10000 20000 30000 40000 50000 30000 40000 50000 100 10000 20000 30000 40000 50000 100-45000 100 1000 20000 30000 40000 50000 100 10000 20000 30000 40000 50000 100 1000 20000 30000 40000 50000 100 1000 20000 30000 40000	Min. Typ. DC 100 17.3 10000 15.6 20000 16.1 30000 17.4 40000 17.4 40000 17.4 50000 13 100 12 10000 15 20000 17 30000 22 40000 17 30000 22 40000 12 50000 25 100 27 10000 21 20000 16 30000 16 30000 16 30000 12 10000 20.7 10000 20.0 20000 17.9 30000 17.9 40000 17.9 30000 27.3 20000 27.3 20000 26.9 30000 22.5 40000 27.3 20000 20.8 50000 100 5.5 10000 20.8 50000 5.5	Min. Typ. Max. DC 50 100 17.3 10000 15.6 20000 16.1 30000 17.4 40000 17.4 40000 17.4 50000 13 100 12 10000 15 20000 17 30000 22 40000 12 50000 25 100 27 10000 21 20000 16 30000 16 30000 12 100 20.7 1000 20.7 10000 20.0 20000 19.3 30000 17.9 40000 17.9 40000 27.3 20000 26.9 30000 27.3 20000 20.8 50000 100 5.5

1. Measured on Mini-Circuits Die Test Board (MB-091). See Characterization TB (Fig.2) Starting Frequency of the device is dependent on the input blocking capacitor value.


Absolute Maximum Ratings²

Ratings		
-40°C to 85°C		
150°C		
1.8W		
17dBm		
7.5V		
-1.6V to -0.5V		
240mA		
-5mA to 0mA		
-1V to 1.2V		

2. Permanent damage may occur if these limits are exceeding. 3. If Vc is open, the measured voltage is 1.33V


We can control the gain by over-writting the Vc. (See Figure 1).

Fig 1. Gain vs. Control Voltage (Vc)



LTA-M1109-D+

Fig. 2 Characterization & Application Test Circuit







Fig 2. Assembly Drawing & Characterization Test Circuit

Note: This block diagram is used for characterization. Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5245B microwave network analyzer

Conditions:

- $\begin{array}{l} 1. \ V_{DD} = 5V, \\ 2. \ V_{GG} \text{ is set to obtain desired I}_{DD} \text{ as shown in specification table.} \\ 3. \ Gain and Return loss: Pin=-25dBm \end{array}$
- 4. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +5 dBm/tone at output.
- Switch ON/OFF sequence:
- 1. To switch the amplifier ON:
- a. Turn ON V_{GG} = -1.5V b. Turn ON V_{GG} = 5V c. Adjust V_{GG} to get I_{DD} = 160mA (Typically, VGG = -0.76V)
- 2. To switch the amplifier OFF:
- a. Tune back $V_{GG} = -1.5V$
- b. Turn OFF V_{DD}
- c. Turn OFF V_{GG}

Fig. 4 Output Power vs. VDET



Assembly and Handling Procedure

Storage 1.

Dice should be stored in a dry nitrogen purged desiccators or equivalent.

2. A.S.

MMIC PHEMT amplifer dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic

protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.

Die Handling and Attachment 3.

ESD

Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficent epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.

Wire Bonding 5.

Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.



Additional Detailed Technical Information

additional information is available on our dash board.

	Data Table					
Performance Data	Swept Graphs					
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)					
Case Style	Die					
Die Ordering and packaging information	Quantity, Package Small, Gel - Pak: 5,10,50,100 KGD* Medium [†] , Partial wafer: KGD*<768 [†] <i>Available upon request contact sales r</i> Refer to AN-60-067	Model No. LTA-M1109-DG+ LTA-M1109-DP+ representative				
Environmental Ratings	ENV80					

*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, Standard Terms); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bond ing and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.