# ULTRA·REL<sup>®</sup> Ceramic Hermetic **Frequency Mixers**

300 MHz to 12 GHz LO Levels 4 to 17 dBm

### **The Big Deal**

- 3-Year Guarantee
- Hermetically sealed LTCC construction
- Low-profile case, 0.06" high
- Priced for outstanding VALUE

### **Product Overview**

Mini-Circuits MAC mixers employ a unique new design and a highly repeatable, tightly controlled, automated process that delivers industry-leading reliability at a remarkably affordable price. Schottky diode quads meeting our strict specifications are bonded to a multilayer integrated LTCC substrate, and then hermetically sealed under a controlled atmosphere with gold-plated covers and eutectic AuSn solder. These passive, doublebalanced mixers have been tested to MIL requirements for gross leak, fine leak, thermal shock, vibration, acceleration, mechanical shock, and HTOL, and every MAC mixer is backed with our 3-year guarantee.

#### Click here for more about the MAC mixer

Feature	Advantages			
Low, Flat Conversion Loss	No need to compensate for variations over frequency.			
Hermetically Sealed	Ideal for use anywhere long-term reliability adds bottom-line value: high moisture areas, busy production lines, high-speed distribution centers, heavy industry, outdoor settings, and unmanned facilities, as well as military applications.			
Rugged LTCC/Hermetic Construction	Demonstrated reliability in harsh, physically abusive environments with high vibration, acceleration, and/or mechanical shock.			
Wide Operating Temperature Range	Guaranteed performance from -55 to +125°C. MAC mixers have also passed thermal shock testing from -55 to +150°C, through 1000 cycles, 15 minutes per cycle.			
Exposed Termination Ends	Our unique case design allows for easy visual inspection of side solder fillets per IPC- A-610 section 8.3.4.6, and features gold-plated terminations for excellent solderability.			
Incredible Performance/Price	Game-changing affordability brings Hi-Rel hermetic mixers within the reach of commer- cial budgets.			

## **Key Features**

Notes



**MAC Series** 

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

# Ceramic, Hermetically Sealed Frequency Mixer wide BAND

### Level 17 (LO Power+17 dBm) 2800 to 8000 MHz

0.29

#### **Maximum Ratings**

Operating Temperature	-55°C to 125°C
Storage Temperature	-65°C to 150°C
RF Power	100 mW
IF Current	40 mA
Permanent damage may occur if any	of these limits are exceeded.

#### **Pin Connections**

LO	10
RF	5
IF	3
GROUND	1,2,4,6,7,8,9

#### **Outline Drawing** A±.010 10 9 8 7 6 PCB Land Pattern \* \* \* \* \* \* \* LID/MARKING AREA B±.010 ----K TYP NDE) с MAX G TYF M TYP Suggested Layout Tolerance to be within ±.002 F TYP-+ -F TYP


	Outli	ine Di	mens	sions	(inch mm)	)
Α	В	С	D	E	F	G
.30	.250	.060		.050	.050	.030
7.62	6.35	1.52		1.27	1.27	0.76
Н	J	К	L	М		wt
.056		.085	.270	.035		grams

6.86

0.89

2 16

Demo Board MCL P/N: TB-956+ Suggested PCB Layout (PL-045)



.044 TRACE WIDTH, 3 PL. (SEE NOTE BELOW)

(SLE WOLE BELOW) NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO43508 WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 02. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTINUIOUS GROUND PLANE. DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

1.42

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. G ECO-002480 ED-14156/17 MAC-80H DJ/CP/AM 200611 Page 2 of 4

#### **Features**

- wide bandwidth, 2800 to 8000 MHz
- · low conversion loss, 6.0 dB typ.
- high L-R isolation, 29 dB typ.
- LTCC double balanced mixer • aqueous washable
- low cost
- · low profile, 0.060" protected by US Patent 7,027,795
- 3-YEAR GUARANTEE The Most Reliable Mixers

#### Applications


- satellite up and down converters
- line of sight links
- defense radar
- defense communications Electrical Specifications at 25°C Condition (MHz) Min Max Units Parameter Тур. Frequency Range, LO/RF 2800 - 8000 MHz DC - 1250 MHz Frequency Range, IF 2800 - 5000 9.1 6.0 Conversion Loss' dB 5000 - 8000 6.5 8.9 28 2800 - 5000 42 \_ LO to RF Isolation dB 5000 - 8000 25 34 2800 - 5000 8 16 \_ LO to IF Isolation dB 5000 - 8000 14 31 2800 - 5000 23 IP3 dBm 5000 - 8000 21 RF Input Power at 1 dB Compression 2800 - 8000 +14 dBm

\*Conversion Loss measured at 30 MHz IF.

#### Typical Performance Data at 25°C and LO=+17dBm

				• • • • • • •		
	uency Hz)	Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
10		11700111	117 dBill	THADIN	Thabin	Thoom
2800.1	2830.1	7.06	57.44	10.35	4.13	2.52
3100.1	3130.1	6.29	43.03	13.43	3.32	2.50
3400.1	3430.1	5.71	43.76	14.86	2.11	2.24
3700.1	3730.1	5.42	44.25	14.69	2.17	1.76
4000.1	4030.1	6.49	41.65	12.39	3.31	1.66
4400.1	4430.1	6.84	31.47	14.33	2.58	1.77
4600.1	4630.1	8.21	36.26	18.13	3.41	1.90
5000.1	5030.1	6.71	31.71	24.64	2.88	1.80
5200.1	5230.1	6.09	32.59	27.40	2.59	2.06
5400.1	5430.1	5.67	36.74	28.65	2.24	2.12
5800.1	5830.1	7.95	39.06	30.29	3.88	2.05
6000.1	6030.1	7.18	46.65	31.00	4.18	2.33
6400.1	6430.1	6.29	40.59	33.09	3.34	2.79
6600.1	6630.1	6.33	37.23	34.29	3.30	3.04
7000.1	7030.1	5.71	33.47	33.57	2.59	2.27
7200.1	7230.1	5.55	31.68	28.11	2.18	2.09
7400.1	7430.1	5.47	32.63	24.17	2.07	1.94
7600.1	7630.1	5.65	35.03	22.67	1.92	1.97
7800.1	7830.1	5.91	30.31	19.57	1.80	2.27
8000.1	8030.1	6.53	26.67	15.63	1.68	2.78

#### **Electrical Schematic**



# **MAC-80H+**




Generic photo used for illustration purposes only CASE STYLE: DZ1650

#### +RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

	Available Tape and Reel at no extra cost
Reel Size	Devices/Reel
7"	20, 50, 100, 200
13"	500,1000

# **Performance Charts**

# **MAC-80H+**



Notes

Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp А. В.

### **\_\_\_**Mini-Circuits

# Designed and Built for Long-Term Reliability in **HOSTILE ENVIRONMENTS**



#### **Qualification Testing**

The table below shows the initial qualification testing performed. If required, parts can be subjected to 100% screening and qualifications testing per MIL standard requirement.

Gross Leak	MIL-STD-202 Method 112, Condition D (100% of all MAC Mixers we ship)
Fine Leak	MIL-STD-202 Method 112, Condition C, Procedure IIIa
Thermal Shock	MIL-STD-202 Method 107 (-55/+100C°, 1000 cycles, 15 minutes) (-55/+150C°, 1000 cycles, 15 minutes)
Vibration	MIL-STD-202 Method 204, Condition D (10-2000Hz sine, 20g, 3 axis, 12 c.y.ea.)
Acceleration	MIL- STD-883 Method 2001, Condition E
Mechanical Shock	MIL-STD-202 Method 213, Condition A
HTOL	MIL-STD-202 Method 108, Condition D (1000 hours, 125°C, at rated LO level)
Multiple Reflow	JESD22-B102
Bend Test	JESD22-B113
Adhesion Strength	Push test >10lb









All Photos courtesv of U.S. Military and NASA

Notes

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

