

Frequency Mixer

MBA-EE7756/6

Level 7 (LO Power +7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : SM2

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	800		2000	MHz
	RF (f _L to f _U)	800		2000	MHz
	IF	0.1		300	MHz
Conversion Loss			7.6		dB
LO-RF Isolation			25		dB
LO-IF Isolation			15		dB

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
GROUND	1, 4, 7, 8, 9
ISOLATE	2, 6