

## Frequency Mixer

## MCA-ED11088A/1

Level 13 (LO Power +13 dBm)

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : DZ883**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1650		2115	MHz
	RF (fL to fU)	1650		2115	MHz
	IF	10		300	MHz
Conversion Loss	Total Range		7.8		dB
LO-RF Isolation			39		dB
LO-IF Isolation			33		dB
IP3 Input			+26		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
CASE GROUND	1, 2, 4, 6, 7, 8, 9