

Termination N-Type

50Ω

DC to 18000 MHz

KARN-50-18+



Generic photo used for illustration purposes only

CASE STYLE: LL718

Connectors	Model
N-Type-Male	KARN-50-18+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.


Features

- wideband coverage, DC to 18000 MHz
- 2 watt rating
- rugged construction
- brass body with trimetal finish

Applications

- cellular communications
- satellite communications
- defense communications
- test set-up

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	wt
1.18	0.56	0.67	0.85	0.787	grams
29.97	14.22	17.02	21.59	19.99	30.0


Electrical Specifications

FREQUENCY (MHz)	IMPEDANCE (OHMS)	RETURN LOSS (dB) MIN.							POWER RATING* (W)
		DC-0.5 GHz	DC-1 GHz	DC-2 GHz	DC-4 GHz	DC-8 GHz	DC-12 GHz	DC-18 GHz	
DC-18000	50	35	35	30	30	26	20	18	2

*At 70°C, derate linearly at 0.025W/°C

Typical Performance Data

Frequency (MHz)	Return Loss (dB)
100	50.21
1000	44.44
2000	41.16
4000	41.02
6000	42.43
8000	32.99
10000	25.82
12000	23.41
14000	24.96
16000	30.24
18000	22.88



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

