

Engineering Development Model

Frequency Synthesizer

KSN-EDR8461/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DK801

ELECTRICAL SPECIFICATIONS 50Ω, over -45°C to +85°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	2022		2123	MHz
Step size		50		kHz
Settling Time Within ±1kHz		14		msec
Output Power	+2	+6	+9	dBm
Phase Noise				
at 100 Hz offset		-67		dBc/Hz
at 1 kHz offset		-72		dBc/Hz
at 10 kHz offset		-99	-94	dBc/Hz
at 100 kHz offset		-122	-117	dBc/Hz
at 1000 kHz offset		-142	-137	dBc/Hz
Integrated SSB Phase Noise		42		dBc
Reference Spurious Suppression		-93		dBc
Comparison Spurious Suppression		-109		dBc
Non-Harm. Spurious Suppression		-90		dBc
Harmonic Suppression		-25		dBc
Supply voltage VCO		5		V
Supply voltage PLL		3.3		V
Supply current VCO		44	52	mA
Supply current PLL		10	18	mA
Reference In (External) Frequency		24		MHz
Reference In (External) Amplitude		1		Vp-p
Reference In (External) Impedance		100		kΩ
Reference In (External) Ph. N @ 1kHz		-145		dBc/Hz
Input Logic Levels Logic high	2.64		3.3	V
Input Logic Levels Logic Low			0.66	V
Digital Lock Detect Locked	2.9		3.3	V
Digital Lock Detect Unlocked			0.4	V
Frequency Synthesizer PLL	ADF4118			

ABSOLUTE MAXIMUM RATINGS	
Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to 100°C
VCO Supply Voltage	6V
PLL Supply Voltage	4.3V
Reference Frequency voltage	5.8Vp-p
Data, Clock & LE levels	3.6V

Power On sequence: Vcc VCO followed by Vcc PLL

Power Off sequence: Vcc PLL followed by Vcc VCO

PIN CONNECTIONS			
RF OUT	3	CLOCK	10
VCC VCO	5	DATA	11
VCC PLL	1	LATCH ENABLE	12
REF IN	7	GROUND	2,4,6,8,13,14
LOCK DETECT	9		

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

