

Engineering Development Model

Voltage Controlled Oscillator

MOS-EDR5668/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : CZ682

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	2163		2250	MHz
Tuning Voltage	0.5		4.5	V
Power Output		+0.5		dBm
Phase Noise				
at 1 kHz offset		-74		dBc/Hz
at 10 KHz offset		-101		dBc/Hz
at 100 KHz offset		-121		dBc/Hz
at 1000 kHz offset		-141		dBc/Hz
Pulling at 12 dBm PK-PK all phases		3.5		MHz
Pushing at Vcc=5V±0.25V		1		MHz/V
Tuning Sensitivity		31 - 41		MHz/V
Harmonic Suppression		-17.5	-10	dBc
3 dB Modulation Bandwidth		11500		kHz
Supply Voltage		5		V
Supply Current			30	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+7V
Absolute Tuning Voltage (Vtune)	+6.5V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	1
GROUND	2,4,6,7,8