

Frequency Mixer

LAVI-ED12787/1D

Level 20 (LO Power + 20 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



CASE STYLE : CK605

Please click "Back", and then click "Contact Us" for Applications support.

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	1270		2500	MHz
	RF (f _L to f _U)	1270		2500	MHz
	IF	170		230	MHz
Conversion Loss	Total Range		8.2		dB
LO-RF Isolation			50		dB
LO-IF Isolation			43		dB
Input IP3			+27		dBm
1 dB Compression			+17		dBm

MAXIMUM RATINGS	
Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to +100°C

PIN CONNECTIONS	
LO	10
RF	2
IF	14
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

Electrical Schematic

