

## Engineering Development Model

### Voltage Controlled Oscillator

### MOS-EDR6459

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : CZ682

| ELECTRICAL SPECIFICATIONS 50Ω      |      |         |      |        |
|------------------------------------|------|---------|------|--------|
| Parameter                          | Min. | Typ.    | Max. | Units  |
| Frequency                          | 2550 |         | 2570 | MHz    |
| Tuning Voltage                     | 0.5  |         | 5    | V      |
| Power Output                       |      | +2.5    |      | dBm    |
| Phase Noise                        |      |         |      |        |
| at 1 kHz offset                    |      | -79     |      | dBc/Hz |
| at 10 KHz offset                   |      | -103    |      | dBc/Hz |
| at 100 KHz offset                  |      | -123    |      | dBc/Hz |
| at 1000 kHz offset                 |      | -143    |      | dBc/Hz |
| Pulling at 12 dBr PK-PK all phases |      | 1       |      | MHz    |
| Pushing at Vcc=5V±0.25V            |      | 2       |      | MHz/V  |
| Tuning Sensitivity                 |      | 18 - 26 |      | MHz/V  |
| Harmonic Suppression               |      | -18     | -12  | dBc    |
| 3 dB Modulation Bandwidth          |      | 230000  |      | kHz    |
| Supply Voltage                     |      | 5       |      | V      |
| Supply Current                     |      |         | 27   | mA     |

| MAXIMUM RATINGS                 |                |
|---------------------------------|----------------|
| Operating Temperature           | -55°C to 85°C  |
| Storage Temperature             | -55°C to 100°C |
| Absolute Supply Voltage (Vcc)   | +7V            |
| Absolute Tuning Voltage (Vtune) | +7V            |

| PIN CONNECTIONS |           |
|-----------------|-----------|
| RF OUT          | 10        |
| VCC             | 14        |
| V-TUNE          | 1         |
| GROUND          | 2,4,6,7,8 |