Ceramic .ow Pass Filter

50Ω DC to 3900 MHz

LFCG-3800+

The Big Deal

- Very good rejection, 50 dB typical
- Rugged, ceramic construction
- Tiny size, 0.079" x 0.049" x 0.037" (0805)
- Excellent power handling, 4.5W



Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

Product Overview

Mini-Circuits' LFCG-3800+ is an LTCC low pass filter with a passband from DC to 3900 MHz, supporting a variety of applications. This model provides 1.3 dB typical passband insertion loss and provides a very good stopband rejection due to strategically constructed layout with minimal interaction between components. It handles up to 4.5W RF input power and provides a wide operating temperature range from -55 to +125°C. Housed in a tiny 0805 ceramic form factor with wraparound terminations, the filter is ideal for dense PCB layouts and with minimal performance variation due to parasitics.

Key Features

Feature	Advantages			
Ultra-wide stopband	The LTCC lowpass filter provides a very good stopband rejection until 18 GHz suitable for high end applications.			
LTCC Construction	Provides repeatable performance in a rugged, ceramic package well suited for tough environments such as high humidity and temperature extremes.			
Tiny size (0.079" x 0.049" x 0.037")	Saves space in dense circuit board layouts and minimizes the effects of parasitics.			
Excellent power handling, 4.5W	Supports a wide range of system power requirements.			
Wrap-around terminations	Provides excellent solderability and easy visual inspection			

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ceramic Low Pass Filter

50Ω DC to 3900 MHz


Features

- Low loss, 1.3 dB typical
- High rejection 50 dB typical
- Excellent power handling, 4.5W
- Extremely small size 0805 (2.0 mm x 1.25 mm)
- Temperature stable


LTCC construction

- Applications
- Harmonic Rejection
- VHF/ UHF transmitters / receivers
- Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications
- Public safety communication
- Satcom modems

Functional Schematic



Typical Frequency Response







Generic photo used for illustration purposes only CASE STYLE: GE0805C-2

+ROHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications^{1,2} at 25°C

Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 3900	_	1.3	1.8	dB
Pass Band	Freq. Cut-Off	F2	5000	_	3.0	_	dB
	Return Loss	DC-F1	DC - 3900	_	14	—	dB
Stop Band	Rejection Loss	F3-F4	5800 - 6200	20	40	_	dB
		F4-F5	6200 - 8400	35	42	_	dB
		F5-F6	8400 - 12000	25	48	—	dB
		F6-F7	12000 - 18000	_	20		dB

1 DC de-coupling capacitors are required in Applications where DC voltage and/or current is present at either input or output ports. Please contact Mini-Circuits for alternatives if DC pass from IN-OUT is required. 2 Measured on Mini-Circuits Characterization Test Board TB-799+

Maximum Ratings				
Operating Temperature	-55°C to 125°C			
Storage Temperature	-55°C to 125°C			
RF Power Input*	4.5W max.@25°C			

*Passband rating, derate linearly to 1W at 125°C ambient Permanent damage may occur if any of these limits are exceeded

Typical Performance Data at 25°C

Typical Ferrormance Data at 25 C					
Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)			
10	0.09	46.99			
100	0.12	39.94			
500	0.18	39.75			
1000	0.25	32.99			
1500	0.33	23.47			
3800	0.82	22.72			
3900	0.87	22.44			
5000	3.58	11.97			
5380	20.59	2.19			
5490	30.36	1.61			
5800	39.45	0.86			
6000	42.37	0.66			
6200	48.44	0.53			
8000	59.93	0.42			
8400	53.65	0.49			
9000	46.61	0.64			
10000	40.21	0.83			
12000	33.47	0.74			
15000	31.92	0.37			
18000	29.42	0.77			



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B ECO-004070 LFCG-3800+ EDU3522 URJ 210317 Page 2 of 3




Pad Connections

INPUT	8
OUTPUT	4
GROUND	1,2,3,5,6,7

Product Marking: LS


Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)



NOTES:

- COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER
 - BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Drawing



Outline Dimensions (inch)

А	В	С	D	Е	F	G	Wt.
.079	.049	.037	.014	.012	.012	.026	grams
2.00	1.25	0.95	0.35	0.30	0.30	0.65	.008

Note: Please refer to case style drawing for details

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp