Low Pass Filter

50 Ω DC¹ to 435 MHz

Features

- Low loss, 0.9 dB typ.
- Small size 0805 (2.0 x 1.25 mm)
- Temperature stable
- LTCC construction

Applications

ATTENUATION

- Automatic meter reading
- Harmonic Rejection
- VHF/UHF transmitters / receivers

Specification Definition

F1 F2 F3 F4 FREQUENCY

LFCG-42+



CASE STYLE: GE0805C-2

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Electrical Specifications^{1,2} at 25°C

Pa	arameter	F#	F# Frequency (MHz) Min. Typ. Max.		Max.	Unit	
	Insertion Loss	DC - F1	DC - 435		0.9	1.6	dB
Pass Band	Freq. cut-off	F2	475	_	3.0	_	dB
	VSWR	DC - F1	DC - 435	_	1.5	_	:1
		F3	625	20	40	_	
Stop Band	Rejection Loss	F4 - F5	650 - 2700	25	30	_	dB
		F6	6000	_	30	_	


¹ In Application where DC voltage is present at either input or output port, coupling capacitors are required.


Maximum Ratings

Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	2W at 25°C

^{*}Passband rating, derate linearly to 1W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

Functional Schematic







Pad Connections

Input	8
Output	4
Ground	1,3,5,7
Isolate (Do not ground)	2,6

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.21	1.01
20	0.13	1.02
100	0.21	1.14
200	0.31	1.15
300	0.42	1.10
435	0.89	1.25
475	1.68	1.64
625	43.44	53.03
650	34.41	60.85
800	32.18	97.11
1000	44.53	115.78
1500	42.44	131.39
2000	43.76	151.39
2700	55.08	158.07
4000	42.79	142.86
5000	37.13	98.40
6000	33.51	88.66







² Measured on Mini-Circuits Characterization Test Board TB-800+

Low Pass Filter LFCG-42+

Outline Drawing



PCB Land Pattern




Suggested Layout, Tolerance to be within .002

Pad Connections

Input	8
Output	4
Ground	1,3,5,7
Isolate (Do not ground)	2,6

Demo Board MCL P/N: TB-800+ Suggested PCB Layout (PL-427)



NOTES:

- 1. COPLANAR WAVEGIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS. 0.10" ± .00.1". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED. 2. BOTTOM SIDE OF THE PCB IS CONTIN
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Outline Dimensions (inch)

G	F	E	D	С	В	Α
.026	.012	.012	.014	.037	.049	.079
0.66	0.30	0.30	0.36	0.94	1.24	2.01
wt		M	L	K	J	Н
wt grams		M .039	L 0.014	.104	J .134	H .025

Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

