# **Low Pass Filter**

# 50Ω 4900 to 6100 MHz


### **Features**

- Low loss, 1 dB typ.
- Small size 0805 (2.0 x 1.25 mm)
- Temperature stable
- · LTCC construction


# **Applications**

- ISM band filtering
- · Harmonic Rejection
- C band transmitters / receivers
- Lab use


#### **Specification Definition**



#### **Functional Schematic**



#### Top View



#### **Pad Connections**

Input	8
Output	4
Ground	1,2,3,5,6,7

# LFCG-612+



Generic photo used for illustration purposes only CASE STYLE: GE0805C-4

#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Electrical Specifications<sup>1,2</sup> at 25°C

Pa	arameter	F#	Frequency (MHz)	lz) Min. Typ. Max.		Unit	
	Insertion Loss	F0 - F1	4900 - 6100		1.0	1.2	dB
Pass Band	Freq. cut-off	F2	7500	_	3.0	_	dB
	VSWR	F0- F1	4900 - 6100	_	1.7	_	:1
		F3	8200	_	20	_	dB
Stop Band	Rejection Loss	F4 - F5	9800 - 12200	33	40	_	dB
		F6	14700 - 18300	25	33	_	dB

<sup>&</sup>lt;sup>1</sup> In Application where DC voltage is present at either input or output port, coupling capacitors are required.


#### **Maximum Ratings**


Operating Temperature	-55°C to +100°C
Storage Temperature	-55°C to +100°C
RF Power Input*	1W at 25°C

<sup>\*</sup>Passband rating, derate linearly to 0.5W at 100°C ambient Permanent damage may occur if any of these limits are exceeded.

# Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.16	1.01
200	0.16	1.26
600	0.63	1.96
1000	1.39	2.90
3000	3.72	6.22
4900	0.78	1.52
6100	0.78	1.24
7500	2.55	1.64
8200	22.02	22.66
9800	43.00	53.85
12200	41.19	74.67
14700	47.48	32.13
16000	52.06	36.96
17000	56.18	124.20
18300	62.88	30.30
20000	44.34	105.03







<sup>&</sup>lt;sup>2</sup> Measured on Mini-Circuits Characterization Test Board TB-799+

# LFCG-612+

# **Outline Drawing**



#### PCB Land Pattern



Suggested Layout, Tolerance to be within±.002


#### **Pad Connections**

Input	8
Output	4
Ground	1,2,3,5,6,7

# Outline Dimensions (inch )

G	F	E	D	С	В	Α
.026	.012	.012	.014	.027	.049	.079
0.66	0.30	0.30	0.36	0.69	1.24	2.01
wt		M	L	K	J	Н
grams		.039	.014	.110	.134	.025
.008		0.99	0.36	2.80	3.40	0.64

#### Demo Board MCL P/N: TB-799+ Suggested PCB Layout (PL-429)



#### NOTES:

- 1. COPLANAR WAVEGUIDE IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" ± .001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
  2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
  - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

# **Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

