

Engineering Development Model

Low Pass Filter SMT

LFCN-ED13263/3

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FV1206

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 1 dB)	1		1200	MHz
fco Nom. (Loss 3 dB)	--	1530	--	MHz
Stopband F 20 (loss, dB)	1865	--	--	MHz
30 (loss, dB)	--	2000-5000	--	MHz
FR 20 (loss, dB)	--	6200	--	MHz
Passband VSWR	--	1.2	--	(:1)
Stopband VSWR	--	20	--	(:1)


MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W at 25°C

*Derate linearly to 3.5W at 100°C ambient.

PIN CONNECTIONS	
RF IN	1**
RF OUT	3**
GROUND	2,4

**RF IN & RF OUT can be interchanged.

Functional Schematic



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350168, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine. Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X1
LFCN-ED13263/3
12/2/2008
Page 1 of 1